



FINAL PRODUCT/PROCESS CHANGE NOTIFICATION #16510A

Generic Copy

Issue Date: 23-May-2013

TITLE: Additional Assembly/Test Site for capacity expansion of Surface Mount Rectifiers in SMA/SMB package. Site Previously Qualified.

PROPOSED FIRST SHIP DATE: 23-Aug-2013

AFFECTED CHANGE CATEGORY(S): Subcontractor Assembly/Test Site (Previously Qualified)

FOR ANY QUESTIONS CONCERNING THIS NOTIFICATION:

Contact your local ON Semiconductor Sales Office or Raja Roziah Raja Rahmat
<Raja.Roziah.Rahmat@onsemi.com>

SAMPLES: Contact your local ON Semiconductor Sales Office or Norfizah Mohd Ariffin
<Norfizah.MohdAriffin@onsemi.com>

ADDITIONAL RELIABILITY DATA: Available

Contact your local ON Semiconductor Sales Office or Laura Rivers <Laura.Rivers@onsemi.com>

NOTIFICATION TYPE:

Final Product/Process Change Notification (FPCN)

Final change notification sent to customers. FPCNs are issued at least 90 days prior to implementation of the change.

ON Semiconductor will consider this change approved unless specific conditions of acceptance are provided in writing within 30 days of receipt of this notice. To do so, contact <quality@onsemi.com>.

DESCRIPTION AND PURPOSE:

ON Semiconductor has previously qualified LiteOn Seeful (China) to assemble/test of SMA/SMB Schottky and Ultrafast Rectifiers per FPCNs 16510, 16012, and 15687. This is the final notification announcing that ON Semiconductor is adding the attached devices for assembly and test in SMA/SMB packages at Liteon Seeful's factory in China for additional capacity to support demands and reduce product leadtimes.



FINAL PRODUCT/PROCESS CHANGE NOTIFICATION # 16510A

RELIABILITY DATA SUMMARY:

MURS260T3G – Ultrafast Rectifier

Test	Conditions	Interval	Results
HTRB	Ta=150C,80% Rated Voltage	1008 hrs	0/240
Precondiitiong	MSL1 @ 260, A113		0/480
Autoclave+PC	Ta=121C RH=100% ~15 psig	96 hrs	0/240
TC+PC	Ta= -65 C to 150 C	1000 cyc	0/240

MBRS1100T1G – Schottky Rectifier

Test	Conditions	Interval	Results
HTRB	Tj=150C,80% Rated Voltage	1008 hrs	0/240
Precondiitiong	MSL1 @ 260, A113		0/960
Autoclave+PC	Ta=121C RH=100% ~15 psig	96 hrs	0/240
H3TRB +PC	Ta=85C RH=85% bias=80% rated V or100V Max	1008 hrs	0/240
IOL+PC	Ta=25C, Delta TJ = 100 C, Ton/off = 2 min.	15000 cyc	0/240
TC+PC	Ta= -65 C to 150	1000 cyc	0/240
RSH	Ta=260C, 10 sec dwell		0/30

ELECTRICAL CHARACTERISTIC SUMMARY:

Product performance meets data sheet specifications.

CHANGED PART IDENTIFICATION:

Devices sourced from Seefull in Shanghai (China) will carry the site code “p” (lower case) on the package marking.



FINAL PRODUCT/PROCESS CHANGE NOTIFICATION # 16510A

List of affected General Parts:

MBRA210ET3G
MBRA210LT3G
MBRA2H100T3G
MBRA320T3G
MBRA340T3G
MURA105T3G
MURA110T3G
MURA115T3G
MURA120T3G
MURA130T3G
MURA140T3G
MURA205T3G
MURA210T3G
MURA215T3G
MURA220T3G
MURA230T3G
MURA240T3G
MBRS120T3G
MBRS130LT3G
MBRS130T3G
MBRS140T3G
MBRS1540T3G
MBRS190T3G
MBRS230LT3G
MBRS260T3G
MBRS2H100T3G
MBRS3200T3G
MBRS360BT3G
MURS230T3G
MURS240T3G
SS22T3G
SS24T3G