

General Information

Extended Product Type:	BJDL5-10
Product ID:	1SNA291110R2600
EAN:	3472592911106
Catalog Description:	BJDL5-10 Jumper Bars
Long Description:	- Jumper bar for spring blocks with the same spacing, - Facilitate & secure your jumper bar assembly process: - Screwless mounting, - Pre-cut poles for alternated jumpering between terminal blocks, - Insulated, - Positive locking.

Additional Information

ABB Industrial IT Suite:	Control IT
Color:	Orange
Country of Origin:	France (FR)
Customs Tariff Number:	39269097
Data Sheet, Technical Information:	1SNC160001C0207-CH-J Accessories
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
EAN:	3472592911106
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block
Function:	Jumper Bars
IT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC160001C0207-CH-J Accessories
Invoice Description:	BJDL5-10 Jumper Bars
Minimum Order Quantity:	20 piece
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Poles:	10
Object Classification Code:	X
Order Multiple:	20 piece
Package Level 1 EAN:	3472592911106
Package Level 1 Gross Weight:	0.024 kg
Package Level 1 Length:	250 mm
Package Level 1 Units:	20 piece
Package Level 1 Width:	168 mm
Package Level 2 Units:	1000 piece
Package Level 3 Units:	180000 piece
Product Main Type:	BJDL
Product Name:	Jumper Bar
Product Net Weight:	1.2 g
Product Packing Type:	Bag
Rated Current (I_n):	Main Circuit 24 A
RoHS Date:	18 08 2005
RoHS Information:	1SND230492F0201
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Selling Unit of Measure:	piece
Short Description:	Jumper Bars BJD5-10
Spacing:	5 mm
Sub-Function 2:	ScrewLess
Suitable For:	D2.5/5.2L D2.5/5.2L.2L D2.5/5.3L D2.5/5.4L D2.5/5.A.L.L D2.5/5.A.L.L.L D2.5/5.A.L.L.P.L D2.5/5.A.N.L D2.5/5.A.N.L.L D2.5/5.A.N.L.P.L D2.5/5.A.N.T.L.P.L D2.5/5.C3.L D2.5/5.C4.L D2.5/5.D2.L D2.5/5.DD.L D2.5/5.DE1.D.L D2.5/5.DE1.L D2.5/5.DE2.D2.L D2.5/5.DE2.L D2.5/5.DL.L D2.5/5.I.3L D2.5/5.L.L D2.5/5.L.L.L D2.5/5.L.L.P.L D2.5/5.N.L D2.5/5.N.L.L D2.5/5.N.L.P.L D2.5/5.N.T.L D2.5/5.N.T.L.P.L D2.5/5.SB.2L D2.5/5.SB.4L D2.5/5.SNB.2L D2.5/5.SNB.4L D2.5/5.SNBT.2L D2.5/5.SNBT.4L D2.5/5.T1.L D2.5/5.T1.P.L D2.5/5.T3.L D2.5/5.T3.P.L DB2.5/5.2L DH2.5/5.2L DR2.5/5.2L DS2.5/5.2L



