# **HS/HSL Supercapacitors**

# Hybrid cylindrical cells



Photo is representative

#### **Description**

Eaton hybrid supercapacitors are high reliability, high power, ultra-high capacitance energy storage devices utilizing proprietary materials and processes. This combination of advanced technologies allows Eaton to offer a wide variety of capacitor solutions tailored to applications for backup power, pulse power and hybrid power systems.

They can be applied as the sole energy storage or in combination with batteries to optimize cost, life time and run time. System requirements can range from a few microwatts to hundreds of watts.

All products feature low ESR for high power density with environmentally friendly materials for a green power solution. Eaton supercapacitors are maintenance-free with design lifetimes up to 20 years\* and operating temperatures down to -25 °C (HSL) and up to +85 °C (HS)

#### Features and benefits

- 3.8 V operating voltage for high energy
- · Low ESR for high power density
- Up to 8 times energy density compared to standard supercapacitors
- · Low self discharge ideal for use with batteries
- · UL recognized

#### **Applications**

- Industrial backup/ride through
- Backup for storage servers
- · Water and gas smart meters
- · IoT energy storage
- Medical backup power/alarm
- · Commercial trucks/containers asset tracking

#### **Environmental compliance**







#### **Agency information**



\*Supercapacitor lifetimes vary based on charge voltage and temperature. See Eaton's application guidelines or contact your local Eaton sales representative for more information on lifetime estimates



#### **Ratings**

Capacitance	5 F to 220 F
Maximum rated working voltage	3.8 V
Minimum rated working voltage	2.5 V
Minimum allowed working voltage	2.2 V
Surge voltage	4.2
Operating temperature range	HSL: -25 °C to +70 °C HS: -15 °C to +70 °C
Extended operating temperature range	HS: -15 °C to +85 °C (with linear voltage derating to 3.5 V @ +85 °C)

# **Specifications**

Capacitance¹ (F)	Capacitance tolerance	Part number	Maximum DC ESR @ +25 °C¹ (mΩ)	Maximum ESR, 1 kHz @ +25 °C¹ (mΩ)	Maximum leakage current <sup>1,2</sup> (μA) HS/HSL	Stored energy³ (mWh)	Peak power⁴ (W)	Rated charge/ discharge current (A)	Maximum charge/ discharge current <sup>5</sup> (A)	Short circuit current <sup>6</sup> (A)
5	-20%/+50%	HS/HSL0612-3R8505-R	6000	2000	2.0/2.5	6.67	0.60	0.025	0.15	0.633
10	±20%	HS/HSL0814-3R8106-R	1500	500	2.0/3.0	13.3	2.4	0.05	0.5	2.5
25	±20%	HS/HSL0820-3R8256-R	650	300	2.5/3.3	33.3	5.5	0.125	0.8	5.8
30	0/+50%	HS/HSL1016-3R8306-R	550	250	3.0/4.0	40	6.6	0.15	1.0	7.0
50	±20%	HS/HSL1020-3R8506-R	450	200	4.0/5.0	67	8.0	0.25	2.0	9.0
70	±20%	HS/HSL1025-3R8706-R	250	100	5.0/8.0	93	14	0.35	3.0	15
120	±20%	HS/HSL1225-3R8127-R	200	70	7.0/12	160	18	0.75	6.0	19
150	±20%	HS/HSL1040-3R8157-R	140	80	9.0/16	200	26	0.60	5.0	27
220	±20%	HS/HSL1625-3R8227-R	100	60	12/25	293	36	1.1	8.0	38

<sup>1.</sup> Capacitance, Equivalent series resistance (ESR) and Leakage current are measured according to internal specifications.

3600

4. Peak power (W) =  $\frac{V^2}{4 \text{ x DC ESR}}$ 

Note: Do not discharge supercapacitors below minimum allowed working voltage

# **Performance**

Parameter	Capacitance change (% of initial value)	ESR AC (% of maximum initial value)
Lifetime: (1000 hours, [HS/HSL]: +70 °C, 3.8 Vdc, [HS]: +85 °C, 3.5 Vdc)	≤ 30%	≤ 200%
Charge/discharge cycles*: HS: (500,000 at +20 °C), HSL: (250,000 at +20 °C)	≤ 30%	≤ 200%
Storage: (3 years, uncharged, <+25 °C)	≤ 15%	≤ 150%

<sup>\*</sup>Cycle: 3.8 V to 2.5 V, 5 s rest @ +20 °C

# Safety and certifications

Agency information	UL810a, UL recognized file number MH46887
Shock and vibration	MIL-STD 202G
Environmental compliance	RoHS, REACH, lead free, halogen free
Warnings	Do not overvoltage, do not reverse polarity
Shipping	Per UN 3508

<sup>2.</sup> Leakage current at +25 °C after 72 hour charge and hold.

3. Stored energy (mWh) = 0.5 x (V² rated - V² min) x C


<sup>5.</sup> Discharge current for 3 seconds from 3.8 V to 2.5 V  $\,$ 


<sup>6.</sup> Short circuit current is for safety information only. Do not use as operating current.


Testing and verification of product under end application conditions is recommended

# **Dimensions (mm)**

Part number	ØD ±0.5	L ±2.0	P ±0.5	Ød ±0.05	L (+) ±3.0	L (-) ±3.0	Voltage/ capacitance marking	RU Mark	Weight(ref) (g)
HS/HSL0612-3R8505-R	6.3	12.0	2.6	0.5	27.0	22.0	3.8V 5F	Yes	0.8
HS/HSL0814-3R8106-R	8.0	14.0	3.5	0.6	27.0	22.0	3.8V 10F	Yes	1.4
HS/HSL0820-3R8256-R	8.0	20.0	3.5	0.6	27.0	22.0	3.8V 25F	Yes	1.8
HS/HSL1016-3R8306-R	10.0	16.0	5.0	0.6	27.0	22.0	3.8V 30F	Yes	2.5
HS/HSL1020-3R8506-R	10.0	20.0	5.0	0.6	27.0	22.0	3.8V 50F	Yes	3.2
HS/HSL1025-3R8706-R	10.0	25.0	5.0	0.6	27.0	22.0	3.8V 70F	Yes	3.8
HS/HSL1225-3R8127-R	12.5	25.0	5.0	0.6	27.0	22.0	3.8V 150F	Yes	5.4
HS/HSL1040-3R8157-R	10.0	40.0	5.0	0.6	27.0	22.0	3.8V 120F	Yes	6.0
HS/HSL1625-3R8227-R	16.0	25.0	7.5	0.8	27.0	22.0	3.8V 220F	Yes	9.4







#### Packaging information-(Bulk package)

	Unit pac	k (Inner bo	c)		Shipping case (Carton)				
		dimensions		Package QTY		dimensions-		Package QTY	Gross weight
Part number	L	W	Н	pcs	L	W	Н	pcs	kg
HS0612-3R8505-R	175.0	170.0	65.0	100	370.0	360.0	215.0	1200	2.8
HS0814-3R8106-R	175.0	170.0	65.0	100	370.0	360.0	215.0	1200	3.5
HS0820-3R8256-R	175.0	170.0	65.0	100	370.0	360.0	215.0	1200	4.2
HS1016-3R8306-R	175.0	170.0	65.0	100	370.0	360.0	215.0	1200	4.8
HS1020-3R8506-R	175.0	170.0	65.0	100	370.0	360.0	215.0	1200	5.7
HS1025-3R8706-R	175.0	170.0	65.0	100	370.0	360.0	215.0	1200	6.4
HS1040-3R8157-R	160.0	152.0	75.0	60	335.0	335.0	245.0	720	6.0
HS1225-3R8127-R	212.0	115.0	70.0	50	440.0	250.0	230.0	600	5.2
HS1625-3R8227-R	212.0	115.0	70.0	36	440.0	250.0	230.0	432	5.6
HS1625-3R8227-1	212.0	115.0	70.0	36	440.0	250.0	230.0	432	5.6
HSL0612-3R8505-R	175.0	170.0	65.0	100	370.0	360.0	215.0	1200	2.8
HSL0814-3R8106-R	175.0	170.0	65.0	100	370.0	360.0	215.0	1200	3.5
HSL0820-3R8256-R	175.0	170.0	65.0	100	370.0	360.0	215.0	1200	4.2
HSL1016-3R8306-R	175.0	170.0	65.0	100	370.0	360.0	215.0	1200	4.8
HSL1020-3R8506-R	175.0	170.0	65.0	100	370.0	360.0	215.0	1200	5.7
HSL1025-3R8706-R	175.0	170.0	65.0	100	370.0	360.0	215.0	1200	6.4
HSL1040-3R8157-R	160.0	152.0	75.0	60	335.0	335.0	245.0	720	6.0
HSL1225-3R8127-R	212.0	115.0	70.0	50	440.0	250.0	230.0	600	5.2
HSL1625-3R8227-R	212.0	115.0	70.0	36	440.0	250.0	230.0	432	5.6

### Part numbering system

нѕ	1020		-3R8	50	6	-R
Family code	Size reference (mm)		Voltage (V) R = decimal	Capacitance (μF) Value  Multiplier		Chandand and dust
HS/HSL = Hybrid supercapacitor	Diameter = 10	Length = 20	3R8 = 3.8 V	Example 506= 50 x 10 <sup>6</sup> μF or 50 F		Standard product

# Manual solder only (Wave and reflow soldering not recommended)

+350 °C (4-5 seconds by soldering iron)

#### Cleaning/Washing

No clean soldering recommended. Do not wash the supercapacitors.

Part marking: (reference only)

Manufactuer RU logo

Polarity Family code or part number

Supercapacitors Voltage, capacaitance

Lot code

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton Electronics Division 1000 Eaton Boulevard Cleveland, OH 44122

United States Eaton.com/electronics

© 2025 Eaton All Rights Reserved Printed in USA Publication No. 11043 Published: August 2025 Follow us on social media to get the latest product and support information.









