

Screw tap, HSSE-PM TiN M ISO 2 (6H) 50° (right) 371 C

For universal use up to 1300 N/mm²

ATORN[®]



Application

For producing metric threads on CNC machines or conventional machines in **blind holes** in the steel, stainless steel, non-ferrous metals and cast iron material groups up to a strength of 1300 N/mm².

Version

- Dimensions to: DIN 371 = reinforced shank (to M10), DIN 376 = protruding shank (from M12)

Advantage

- Long service life and process reliability through innovative cutting geometry and universal use for maximum application flexibility

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	18	13	10	10	9	19	19	17	19	17	17	15	16	18					

Art. No.	13056 100
Type	UNI 50 Control
Thread type	Metric thread
Thread type x nominal diameter	M10
Pitch	1.5 mm
Hole type	Blind hole ≤ 2.5xD
Cutting material	HSSE-PM
Surface	TiN
Lead angle shape	C
Tolerance of screw taps	ISO 2 (6H)
Twist angle	50° (right)
Shaft diameter	10 mm
Application type/machine type	CNC, Conventional
Core hole diameter	8.5 mm
Coolant supply	External
Length	100 mm
Shank square	8 mm
Cutting speed (steel 1000) suitability	1
Cutting speed (steel 1300) suitability	2
Overall stainless steel suitability	1
fitness not iron total	1
fitness Titan/Nickel/Super total	3
Cutting speed (cast) suitability	1
Cutting speed (hard 55) suitability	3
Cutting speed (hard 65) suitability	3
DIN	371

EAN-Code

4050293188400