Rubber Endstop Buffers • truncated cone form

25150.0738

Product Description

To be used as an elastic end-stop, bearing foot etc.
The hardness is 55 ±5° shore A. Further shore hardnesses (40 ±5° shore A and 70 ±5° shore A) on request.

Material

Support washer
- Steel, zinc-plated by galvanization, passivated

Threaded bushing
- Steel, zinc-plated by galvanization, passivated

Body
- NBR

More information

Further products

- Support Legs, impact cushioning
- Silicone Endstop Buffers, truncated cone form

Drawing



picture 1



picture 2

Order information

Dimensions						Spring rate R ~	Load capacity max.	Spring range ~				Art. No.
d_1	d_2	d_3	l_1	s	t ~				min.	max.		
[mm]						[N/mm]	[N]	[mm]	[°C]		[g]	
with female thread – picture 1, Steel												
38	**M8**	24.5	32	2	8	125	1200	9.5	-30	80	43	25150.0738

Compliance

RoHS-compliant
Compliant with Directive 2011/65/EU [RoHS].

Does not contain SVHC substances
No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 25.06.2025.

SCIP-code
N/A

Does not contain Proposition 65 substances
No Proposition 65 substances included.
https://www.P65Warnings.ca.gov/

Free from Conflict Minerals
This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.

POP-compliant
Contains no persistent organic pollutants – Stockholm Convention [POP] as of September 2025.

PFAS-compliant
Contains no per- and polyfluoroalkyl substances (PFAS).

TSCA-compliant
Agent concentration in this product does not exceed the specified threshold.