

Thread limit plug gauge

For standard metric ISO thread // improved corrosion resistance

ATORN[®]

Application

For testing the flank diameter of female threads and compliance with minimum dimensions of the external diameter.



Version

- Surface hardness approx. 2500 Vickers

Advantage

- Improved corrosion resistance
- Wear resistance approx. 10 times greater than conventional gauge steel
- Extended calibration intervals
- Cost reduction

Art. No.	32696 120
Calibration Group	AA
Thread type	Metric thread
Thread type x nominal diameter x pitch	M12 x 1.75
Pitch	1.75 mm
Tolerance class	6H
Material	TiN
DIN	2280

EAN-Code

4050293202472