


Model 5543B Electronic DMM Test Lead Kit



FEATURES:

- Kit contains a pair of test leads and a pair of test probes and one each of the accessories above
- Fits Fluke, H-P, Tektronix, Wavetek and Amprobe DMM's with sheathed style safety jacks.
- Flexible test leads feature high strand count silicone wire for extreme flexibility and high temperature. resistance. Banana plugs are molded directly to the wire for superior pull strength.
- Extended slide-on tip adapter fits directly over the probe tip, for hard to reach test point. Tip is insulated to the point, to avoid shorting of adjacent components.
- Probe Body, Medium alligator or Minipincer® Lead attaches directly to the flexible test leads for test versatility.
- Tri-fold pouch of durable nylon conveniently stores the test accessories.
- Insulated Spage Lugs are compatible with screw sizes #10 to 1/4" (M4 to M6).

RATINGS: IEC 1010 2-031, Category II, P2 Compliant, Operating Voltage: 300 VRMS/DC Max. Current: 5 Amperes Max.

ORDERING INFORMATION: 5543B (Kit includes one each of medium alligator, spade lug, Minigrabber® test lead, extended tip, IC tip adapter, tri-fold pouch and two each of the probe body and test leads)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA