



Temperature measuring instrument (1-channel)

testo 926 - The allrounder in temperature measurement



- _____ Ideally suited to applications in the food sector
- _____ Wireless measurement with radio probes possible
- _____ Audible alarm (adjustable limit values)
- _____ TopSafe, the indestructible protective cover, protects from dirt and impact
- _____ Min./max. value store
- _____ Automatic recognition of final value (Auto-hold)
- _____ Certified according to EN 13485



The testo 926 is an exact temperature measuring instrument which is particularly suited to applications in the food sector. In addition to the broad selection of classical probes with a cable, a wireless radio probe can also be connected if required. The dishwasher-safe TopSafe protects the instrument from dirt, water and impact. As the user, you can store limit values in the instrument yourself; as soon as these upper and lower values are violated, an audible warning signal sounds. This alarm

function and the automatic final value recognition simplify measurement, and support you in recognizing and interpreting the measurement values correctly. In addition to this, the instrument reliably stores the minimum and maximum measurement values. testo 926 conforms to HACCP as well as EN 13485. This makes it the ideal partner for large kitchens, hotels, restaurants or in the food industry.

Technical data

testo 926

testo 926-1, 1 channel food temperature measuring instrument T/C Type T, audible alarm, connection to an optional radio probe, with battery and calibration protocol

Part no. 0560 9261



testo 926, Starter set

testo 926, Starter set, 1 channel food temperature measuring instrument T/C Type T, incl. TopSafe, standard immersion/penetration probes, battery and calibration protocol

Part no. 0563 9262

Sensor type

Type T (Cu-CuNi) or NTC and Type K if radio immersion/penetration probes are used

Measuring range	-50 to +400 °C
Accuracy ±1 digit	±0.3 °C (-20 to +70 °C) ±(0.7 °C ±0.5% of mv) (remaining range)
Resolution	0.1 °C (-50 to +199.9 °C) 1 °C (remaining range)

General technical data

Operating temperature	-20 to +50 °C
Storage temperature	-40 to +70 °C
Battery type	9V block battery, 6F22
Battery life	200 h (connected probe, backlight off) 45 h (radio mode, backlight off) 68 h (connected probe, backlight always on) 33 h (radio mode, backlight always on)
Dimensions	182 x 64 x 40 mm
Housing material	ABS
Weight	171 g
Warranty	2 years
Standard	EN 13485



TopSafe, protection of the measuring instrument against impact, dirt and water, dishwasher-proof (optional)



Wireless measurement with radio probes possible (optional)



Measurement data printout on site on the Testo fast printer





Connection for external probes and charger


Accessories

Accessories for measuring instrument	Part no.	
9V rech. battery for instrument, instead of battery	0515 0025	
Recharger for 9V rechargeable battery, for external recharging of 0515 0025 battery	0554 0025	
Radio module for upgrading measuring instrument with radio option		
Radio module for measuring instrument, 869.85 MHz, approval for the countries: DE, FR, UK, BE, NL, ES, IT, SE, AT, DK, FI, HU, CZ, PL, GR, CH, PT, SI, MT, CY, SK, LU, EE, LT, IE, LV, NO	0554 0188	
Radio module for measuring instrument, 915.00 MHz FSK, approval for USA, CA, CL	0554 0190	
Printer and Accessories		
Testo fast printer IRDA with wireless infrared interface; 1 roll thermal paper; 4 AA batteries	0554 0549	
Spare thermal paper for printer (6 rolls), permanent ink measurement data documentation legible for up to 10 years	0554 0568	
External fast charger for 1-4 AA rech. batteries, incl. 4 Ni-MH rech. batteries with individual cell charging and charge control display, incl. impulse trickle charging, integrated discharge function, with built-in international mains plug, 100-240 V, 300 mA, 50/60 Hz	0554 0610	
Transport and Protection		
TopSafe, protects from impact and dirt	0516 0220	
Transport case for measuring instrument, 3 probes and accessories (430 x 310 x 85 mm)	0516 0200	
Transport case for meas. instr. and probes (405 x 170 x 85 mm)	0516 0201	
Case for measuring instrument and probes	0516 0210	
Calibration Certificates		
ISO calibration certificate/temperature for air/immersion probes, calibration points -18°C; 0°C; +60°C	0520 0001	
ISO calibration certificate/temperature for air/immersion probes, calibration point -18°C	0520 0061	
ISO calibration certificate/temperature for air/immersion probes, calibration point 0°C	0520 0062	
ISO calibration certificate/temperature for air/immersion probes, calibration point +60°C	0520 0063	
ISO calibration certificate/temperature for air/immersion probes, calibration points -8°C; 0°C; +40°C	0520 0181	
ISO calibration certificate/temperature meas. instr. with surface probe; calibration points +60°C; +120°C; +180°C	0520 0071	
ISO calibration certificate/temperature single point calibration for surface thermometer; calibration point +60°C	0520 0072	
ISO calibration certificate/temperature single point calibration for surface thermometer; calibration point +120°C	0520 0073	


Radio probes

Radio probes for immersion/penetration measurements					Part no.
Radio immersion/penetration probe, NTC, approval for the countries: DE, FR, UK, BE, NL, ES, IT, SE, AT, DK, FI, HU, CZ, PL, GR, CH, PT, SI, MT, CY, SK, LU, EE, LT, IE, LV, NO; Radio freq. 869.85 MHz FSK					0613 1001
Radio immersion/penetration probe, NTC, approval for USA, CA, CL; Radio freq. 915.00 MHz FSK					0613 1002
Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	Resolution	t_{99}	
	-50 to +275 °C	±0.5 °C (-20 to +80 °C) ±0.8 °C (-50 to -20.1 °C) ±0.8 °C (+80.1 to +200 °C) ±1.5 °C (remaining range)	0.1 °C	t_{99} (in water) 12 s	

Radio handles with probe head for air-/ immersion-penetration-meas.					Part no.
Radio handle for plug-in probe heads, incl. T/C adapter, approval for the countries: DE, FR, UK, BE, NL, ES, IT, SE, AT, DK, FI, HU, CZ, PL, GR, CH, PT, SI, MT, CY, SK, LU, EE, LT, IE, LV, NO; Radio freq. 869.85 MHz FSK					0554 0189
T/C probe head for air/immersion/penetration measurement (T/C Type K)					0602 0293
Radio handle for plug-in probe heads, incl. T/C adapter, approval for USA, CA, CL; Radio freq. 915.00 MHz FSK					0554 0191
T/C probe head for air/immersion/penetration measurement (T/C Type K)					0602 0293
Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	Resolution	t_{99}	
	-50 to +350 °C Short-term to +500 °C	Radio handle: ±(0.5 °C +0.3% of m.v.) (-40 to +500 °C) ±(0.7 °C +0.5% of m.v.) (remaining range) T/C probe head: Class 2	0.1 °C (-50 to +199.9 °C) 1.0 °C (remaining range)	t_{99} (in water) 10 s	

Radio handles with probe head for surface measurement					Part no.
Radio handle for plug-in probe heads, incl. T/C adapter, approval for the countries: DE, FR, UK, BE, NL, ES, IT, SE, AT, DK, FI, HU, CZ, PL, GR, CH, PT, SI, MT, CY, SK, LU, EE, LT, IE, LV, NO; Radio freq. 869.85 MHz FSK					0554 0189
T/C probe head for surface measurement (T/C Type K)					0602 0394
Radio handle for plug-in probe heads, incl. T/C adapter, approval for USA, CA, CL; Radio freq. 915.00 MHz FSK					0554 0191
T/C probe head for surface measurement (T/C Type K)					0602 0394
Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	Resolution	t_{99}	
	-50 to +350 °C Short-term to +500 °C	Radio handle: ±(0.5 °C +0.3% of m.v.) (-40 to +500 °C) ±(0.7 °C +0.5% of m.v.) (remaining range) T/C probe head: Class 2	0.1 °C (-50 to +199.9 °C) 1.0 °C (remaining range)	5 s	

Radio probes

Radio handles for attachable T/C probes			Part no.
Radio handle for plug-in probe heads, incl. T/C adapter, approval for the countries: DE, FR, UK, BE, NL, ES, IT, SE, AT, DK, FI, HU, CZ, PL, GR, CH, PT, SI, MT, CY, SK, LU, EE, LT, IE, LV, NO ; Radio freq. 869.85 MHz FSK			0554 0189
Radio handle for plug-in probe heads, incl. T/C adapter, approval for USA, CA, CL; Radio freq. 915.00 MHz FSK			0554 0191
Illustration	Measuring range	Accuracy	Resolution
	-50 to +1000 °C	±(0.7 °C +0.3% of mv) (-40 to +900 °C) ±(0.9 °C +0.5% of mv) (remaining range)	0.1 °C (-50 to +199.9 °C) 1.0 °C (remaining range)

Technical data Radio probes

Radio immersion/penetration probe, NTC

Battery type	2 x 3V button cell (CR 2032)
Battery life	150 h (meas. rate 0.5 s) 2 months (meas. rate 10 s)









Radio handle

Battery type	2 AAA micro batteries
Battery life	215 h (meas. rate 0.5 s) 6 months (meas. rate 10 s)

Common Technical Data




Measuring rate	0.5 s or 10 s, adjustable on handle
Radio coverage	Up to 20 m (without obstructions)
Radio transmission	Unidirectional
Operating temperature	-20 to +50 °C
Storage temperature	-40 to +70 °C

Probes

Probe type	Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	t ₉₉	Part no.
Food probes					
Robust food penetration probe with special handle, reinforced cable (PVC), T/C Type T, Fixed cable		-50 to +350 °C	±0.2 °C (-20 to +70 °C) Class 1 (remaining range) ¹⁾	6 s	0603 2492
Frozen food probe, corkscrew design, T/C Type T, Plug-in cable		-50 to +350 °C	±0.2 °C (-20 to +70 °C) Class 1 (remaining range) ¹⁾	8 s	0603 3292
Stainless steel food probe (IP67) with PUR cable, T/C Type T, Fixed cable		-50 to +350 °C	±0.2 °C (-20 to +70 °C) Class 1 (remaining range) ¹⁾	7 s	0603 2192
Stainless steel food probe (IP67), with FEP cable to +200 °C, TC Type T, Fixed cable		-50 to +350 °C	±0.2 °C (-20 to +70 °C) Class 1 (remaining range) ¹⁾	7 s	0603 3392
Waterproof, super-quick needle probe for measurements without visible penetration hole, T/C Type T, Fixed cable		-50 to +250 °C	±0.2 °C (-20 to +70 °C) Class 1 (remaining range) ¹⁾	2 s	0628 0027
Quick needle probe to monitor cooking in oven, T/C Type T, Fixed cable		-50 to +250 °C	±0.2 °C (-20 to +70 °C) Class 1 (remaining range) ¹⁾	2 s	0628 0030
Measurement tip with T/C adapter Type T, ideal for fast-action measurement on incoming goods		-50 to +350 °C	Class 1 ¹⁾	5 s	0628 0023
Flexible oven probe, Tmax +250 °C, PTFE cable		-50 to +250 °C	Class 1 ¹⁾		0603 0646

1) According to standard EN 60584-2, the accuracy of Class 1 refers to -40 to +350 °C (Type T).

Probes

Probe type	Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	t ₉₉	Part no.
Air probes					
Robust, affordable air probe, T/C Type T, Fixed cable 1.2 m		-50 to +350 °C	±0.2 °C (-20 to +70 °C) Class 1 (remaining range) ¹⁾	25 s	0603 1793
Surface probes					
Waterproof surface probe with widened measurement tip for flat surfaces, T/C Type T, Fixed cable 1.2 m		-50 to +350 °C	±0.2 °C (-20 to +70 °C) Class 1 (remaining range) ¹⁾	30 s	0603 1993
Immers./penetr. probes					
Waterproof standard immersion/penetration probe, T/C Type T, Fixed cable		-50 to +350 °C	±0.2 °C (-20 to +70 °C) Class 1 (remaining range) ¹⁾	7 s	0603 1293

1) According to standard EN 60584-2, the accuracy of Class 1 refers to -40 to +350 °C (Type T).

