

## Flexible diamond honing stone in cardboard box

6220J standard

**3M**

### Application:

For sharpening and honing of engraving irons, chisels, bevelled-edge chisels and tool cutting edges and for smoothing cut edges on glass, stone and all hard materials.

### Execution:

- The flex diamond material is glued to a 10 mm thick aluminium plate
- Glued on the underside with plastic buffer

### Advantage:

- Meets highest standards of surface quality, with excellent cutting performance and extraordinary finish
- Non-slip properties on smooth backing due to plastic buffer

### Delivery:

In cardboard box



<b>Art. no.</b>	<b>69359 015</b>
<b>Brand</b>	3M
<b>Manufacturer Part Number</b>	7000082274
<b>Surface structure</b>	Fine
<b>Grid size</b>	N040
<b>Length</b>	150 mm
<b>Width</b>	50 mm
<b>Number of pieces per packet</b>	1 PCS
<b>Form</b>	Rectangular
<b>Length x width</b>	150 x 50 mm
<b>Type description</b>	6220J standard
<b>Material of abrasive medium</b>	Diamond
<b>Gross Weight</b>	0.218 kg
<b>Product Group</b>	6DM

### EAN

0051144843671