


AS-Interface CompactLine module

CompactM12 4 DI V4A



Electrical data

Operating voltage	[V]	26.5...31.6 DC; ("supply class 2" to cULus)
Max. current consumption from AS-i	[mA]	250

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 4
------------------------------	-----------------------------

AC2456



AS-Interface CompactLine module

CompactM12 4 DI V4A

Inputs						
Number of digital inputs			4			
Input circuit of digital inputs			PNP			
Sensor supply of the inputs			AS-i			
Voltage supply	[V]		20...30			
Max. total current rating of inputs	[mA]		200			
Input current limitation	[mA]		15			
Input current High	[mA]		6...10			
Input current Low	[mA]		0...2			
Min. switching level high signal	[V]		11			
Digital inputs protected against short circuits			yes			
Operating conditions						
Ambient temperature	[°C]		-25...80			
Protection			IP 67; (when flat cables are used E7400x / E7401x)			
Tests / approvals						
EMC		EN 50295				
AS-i classification						
AS-i version			2.11 + 3.0			
AS-i addressing			IR addressing possible			
Extended addressing mode possible			yes			
AS-i profile			S-0.A.E			
AS-i I/O configuration	[hex]		0			
AS-i ID code	[hex]		A.E			
AS-i certificate			126501			
Assignment of the data bits		data bit	D0	D1	D2	D3
		input	1	2	3	4
		socket	I-1	I-2	I-3	I-4
		pin	4	4	4	4
Mechanical data						
Weight	[g]		285.5			
Type of mounting			AS-i flat cables directly connectable			
Materials			PA 6.6; socket: stainless steel (1.4404 / 316L); threaded inserts in the lower part: stainless steel (1.4404 / 316L); O-ring: EPDM; piercing contacts: CuSn6 nickel-plated and tin-plated; screws stainless steel (1.4578 / 316Cu)			
Displays / operating elements						
Display		operation		LED, green		
		errors		LED, red		
		function		LED, yellow		
Accessories						
Accessories (optional)			Stainless steel sleeve, for installation in case of high mechanical stress , E70402			
Remarks						
Pack quantity			1 pcs.			

AC2456



AS-Interface CompactLine module

CompactM12 4 DI V4A

Electrical connection

Inputs

- | | |
|---|-----------------------|
| 1 | Sensor supply + |
| 2 | not used |
| 3 | Sensor supply - |
| 4 | data input |
| 5 | functional earth (FE) |

Connector: M12

