


# DIN RAILS

## STANDARD AND PRE-CUT LENGTHS

### 35 x 7.5 mm AND 35 x 15 mm

#### DRTB-RAIL Series




DRTB-RAIL-3575-1, 35 x 7.5 mm DIN rail, 1 m (3.3') L shown smaller than actual size.

DRTB-RAIL-SBKT, DIN rail stand-off brackets, sold separately.

- Steel with Electrolytic Zinc Plating
- Available in 1 m (3.3') or 2 m (6.6') Lengths
- Pre-Cut Lengths for Standard Sub-Panel Widths
- Stand-Off Brackets: 45° Angle and Straight
- Comply with DIN 50045, 50022 and 50035 Standards

For Terminal Blocks and Power Supplies Visit us online!



### To Order

MODEL NO.	DESCRIPTION
DRTB-RAIL-3575-1	35 x 7.5 mm (1.4 x 0.3") slotted DIN rail, 1 m (3.3')
DRTB-RAIL-3575	35 x 7.5 mm (1.4 x 0.3") slotted DIN rail, 2 m (6.6')
DRTB-RAIL-3515-1	35 x 15 mm (1.4 x 0.6") slotted DIN rail, 1 m (3.3')
DRTB-RAIL-3515	35 x 15 mm (1.4 x 0.6") slotted DIN rail, 2 m (6.6')
<b>PRE-CUT 35 x 7.5 mm DIN RAIL FOR SUB-PANELS</b>	
MODEL NO.	LENGTH mm (inch) DESCRIPTION
DRTB-RAIL-4	69.9 (2.75) Pre-cut DIN rail for 4" sub-panel width
DRTB-RAIL-6	121 (4.75) Pre-cut DIN rail for 6" sub-panel width
DRTB-RAIL-8	171 (6.75) Pre-cut DIN rail for 8" sub-panel width
DRTB-RAIL-10	222 (8.75) Pre-cut DIN rail for 10" sub-panel width
DRTB-RAIL-12	273 (10.75) Pre-cut DIN rail for 12" sub-panel width
DRTB-RAIL-14/16	324 (12.75) Pre-cut DIN rail for 14 and 16" sub-panel width
DRTB-RAIL-20	425 (16.75) Pre-cut DIN rail for 20" sub-panel width
DRTB-RAIL-24	527 (20.75) Pre-cut DIN rail for 24" sub-panel width
<b>STAND-OFF BRACKETS</b>	
MODEL NO.	DESCRIPTION
DRTB-RAIL-SBKT-45D-6PK	45° DIN rail bracket, package of 6
DRTB-RAIL-SBKT-1-6PK	DIN rail stand off bracket 25 mm (1"), package of 6
DRTB-RAIL-SBKT-2-6PK	DIN rail stand off bracket 51 mm (2"), package of 6
DRTB-RAIL-SBKT-3-6PK	DIN rail stand off bracket 76 mm (3"), package of 6

Ordering Examples: DRTB-RAIL-3575-1, 35 x 7.5 mm (1.4 x 0.3") DIN rail, 1 m (3.3') long, and DIN-RAIL-SBKT-45D-6PK, 45° stand-off bracket. DRTB-RAIL-3575-1, 35 x 7.5 mm DIN rail, 1 m (3.3') long.