

Thermal Magnetic Circuit Breakers

Single Pole - B Curve

pro-ELEC

RoHS
Compliant



Features

- Rated voltage (Un) : 230V AC
- Breaking Capacity : 6kA, 10kA
- Type of terminal : Lug type
- Terminal Capacity : Cable up to 25mm²
- Width : 17.6mm/module
- Dimensions (H×W×D) : 83mm×17.6mm×74mm
- IEC60898, EN60898
- DIN Rail Mount

Part Number Table

Description	Part Number
Thermal Magnetic Circuit Breaker, Single Pole, 6A, 230V AC, 6kA	AUB1 6A
Thermal Magnetic Circuit Breaker, Single Pole, 10A, 230V AC, 6kA	AUB1 10A
Thermal Magnetic Circuit Breaker, Single Pole, 16A, 230V AC, 6kA	AUB1 16A
Thermal Magnetic Circuit Breaker, Single Pole, 20A, 230V AC, 6kA	AUB1 20A
Thermal Magnetic Circuit Breaker, Single Pole, 32A, 230V AC, 6kA	AUB1 32A
Thermal Magnetic Circuit Breaker, Single Pole, 40A, 230V AC, 6kA	AUB1 40A
Thermal Magnetic Circuit Breaker, Single Pole, 50A, 230V AC, 6kA	AUB1 50A
Thermal Magnetic Circuit Breaker, Single Pole, 63A, 230V AC, 6kA	AUB1 63A
Thermal Magnetic Circuit Breaker, Single Pole, 6A, 230V AC, 10kA	AUB7 1P B6A
Thermal Magnetic Circuit Breaker, Single Pole, 10A, 230V AC, 10kA	AUB7 1P B10A
Thermal Magnetic Circuit Breaker, Single Pole, 16A, 230V AC, 10kA	AUB7 1P B16A
Thermal Magnetic Circuit Breaker, Single Pole, 20A, 230V AC, 10kA	AUB7 1P B20A
Thermal Magnetic Circuit Breaker, Single Pole, 32A, 230V AC, 10kA	AUB7 1P B32A
Thermal Magnetic Circuit Breaker, Single Pole, 40A, 230V AC, 10kA	AUB7 1P B40A
Thermal Magnetic Circuit Breaker, Single Pole, 50A, 230V AC, 10kA	AUB7 1P B50A
Thermal Magnetic Circuit Breaker, Single Pole, 63A, 230V AC, 10kA	AUB7 1P B63A

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

pro-ELEC