

Wiha T-Handle, Flag and Key Handle.

The Wiha T-handle, flag and key kandle demonstrate their strengths whenever loosening particularly tight screws and fastening screws with high torque values.

Mature handle concepts enable the use of the complete handle geometry so that it is used as a lever, offering optimum axial power transmission from the hand to the screw.



Wiha T-Handle.

ch that the

ke can be used,

senabling optimum

The ergonomic handle shape permits powerful torque transmission from handle to blade to screw.

The injection moulded T-handle with angled ends permits a good transmission of force from handle to blade. Since the blades are exposed to a high load, Wiha only uses high-quality chromevanadium steels, which, with their through-hardened blades, demonstrate high resistance to wear.


Wiha Flag and Key Handles.

Screwdrivers with these two special handle shapes are always used whenever replacing indexable inserts on milling heads or when carrying out high-torque adjustment work.

Thanks to the flag or key area below the shaft, it is possible to tighten or loosen screws comfortably with a delicate movement.

The cylindrical shaft of the handle is then used to quickly turn the screw in or out.








Wiha T-Handle.

Hex Driver with MagicRing®.





Chrome-vanadium steel, through hardened, nickel plated.

Handle: Wiha T-handle.

Blade:

Application: For high torque transfer with low effort.

Extra: MagicRing® made from spring metal holds all standard screws

tight at various angles (available from 3 mm).

Order-No.	01	-	=		! 1.	-	
22168 3	3	100	126	80	26	10	
22170 6	4	150	176	80	26	10	
22172 0	5	150	182	100	32	10	
22174 4	6	150	182	100	32	10	
21960 4	8	200	232	100	32	10	
219628	10	200	238	120	38	10	

Ballpoint Hex Driver.







540	Ballpoint hex driver with T-handle.
Blade:	Chrome-vanadium steel through hardened nickel plated

Handle: Wiha T-handle.

Application: For high torque transfer with low effort, especially for hard to

reach screws.

Extra: The ballpoint enables the user to work at angles up to 25°.

01	=	=		1.	-	
4	150	176	80	26	10	868-700
5	150	182	100	32	10	848-712
6	150	182	100	32	10	868-724
8	200	238	100	32	10	140-736
10	200	238	120	38	10	
	5 6 8	4 150 5 150 6 150 8 200	4 150 176 5 150 182 6 150 182 8 200 238	4 150 176 80 5 150 182 100 6 150 182 100 8 200 238 100	4 150 176 80 26 5 150 182 100 32 6 150 182 100 32 8 200 238 100 32	4 150 176 80 26 10 5 150 182 100 32 10 6 150 182 100 32 10 8 200 238 100 32 10



334R VB Hex driver set with T-handle.

With MagicRing®, nickel-plated, in bench stand, 6-pcs.

Extra: Stable metal bench stand to stand or hang. Tip symbols printed

to scale.

Order-No. 22096 9	Bench stand equipped								
	extra		6x150	8x200	10x200				
22095 2	Bench s	stand emp	1						