

SDQC boring bar HSS positive, left-hand

For longitudinal and copy turning with DC indexable insert

ATORN[®]

Application

For longitudinal and copy turning with DC indexable insert 55°.

Version

- Precision-made boring bar, **HSS**, with internal cooling, type D, attack angle 107.5°, tip angle 55°, clearance angle 7°

Advantage

- Very narrow geometry optimised for contour-turning work
- Positive body geometry ensures low cutting forces
- Very high rigidity and very good cut quality due to HSS base material



Art. No.	17848 080
ISO name	AH08K SDQC R/L 07
Min. bore diameter	12 mm
Shaft diameter	8 mm
Clearance length	20 mm
Length	125 mm
Clamping surface height	7 mm
Programming size	8 mm
Suitable for indexable inserts	DC.. 0702..
Tool design	Left

EAN-Code

4050293692143