

Revolving centring point

With extended moving point



Application:

For fine turning, rough machining and copying on lathes.

Execution:

- With extended moving point 60°/30°.
- Body and moving point are hardened and ground.
- Moving point can be reground multiple times.

Advantage:

- Special seal prevents the ingress of dirt and coolant.
- Precision roller bearings ensure a high level of concentricity.
- Maintenance-free owing to permanent lubrication.

Delivery:

1x revolving centring point.



Art. no.	22127 050
Brand	RÖHM
Manufacturer Part Number	58672
Morse taper size	MK 5
Programming size	143.5 mm
Programming size for housing	78.5 mm
Max. workpiece weight	1200 kg
Max. rotation speed	3000 rpm
Concentricity tolerance	0.005 mm
Diameter of housing	90 mm
Tip diameter	40 mm
Gross Weight	5.028 kg
Product Group	201

EAN

4019208017082