

Plunge Router Attachment - Model 335

Converts your corded Rotary Tool into a plunge router.



Routs decorative edges.

- · Clear base.
- Two depth stops.
- Includes edge guide and circle guide.
- Rout circles, parallel to edge, signs and inlay work and decorative edges.



Routs accurate circles.

400 398 395 285 275 800 780 770 750

Grout Removal

Attachment – Model 568

For use on wall and floor grout!

- Multiple slide depth adjustment
- 30° angle for controlled cutting
- Guides 180° apart to keep bit centered between tiles
- · Easy screw on mounting
- · Excellent cutting visibility
- Includes 1/16" Grout Removal Bit Model 569. Made of solid carbide, the bit will remove both wall and floor grout.



 Also available: Model 570 1/8" Grout Removal Bit (Not included with 568)





Cutting Kits

Provide controlled cutting in a variety of materials.

- Allows for sturdy controlled cuts with maximum visibility.
- Easy depth adjustment. Set to the correct cutting depth for the material you are working on.
- 1 Multi position depth adjustment
- 2 Easy screw on mounting
- 3 Open arch offers excellent cutting visibility





Multipurpose Cutting Kit – Model 565


Includes cutting guide, 2 drywall cutting bits for cutting drywall for electrical boxes & air vents, and 1 multipurpose cutting bit for making cuts in ceiling tile, wood, plastic, fiberglass, drywall, laminate and vinyl siding.

							1	
400	398	395	285	275	800	780	770	750
•	•	•	•	•	•	•		

Tile Cutting Kit – Model 566

Includes cutting guide and (1) tile cutting bit for shaping ceramic wall tile around fixtures or plumbing pipes.

Not for use on ceramic floor tile.



TOOLS NOT INCLUDED WITH ATTACHMENTS

Attachments

Attachments


DREMEL WORK STATION

Model 220

Functions as an articulating drill press that rotates 90°, rotary tool holder, and flex-shaft tool stand.

- Detents click the tool in place in 15° increments from vertical to horizontal.
- "Crow's Nest" provides on-board storage for Dremel accessories.
- Durable, die-cast aluminum base.

Available February 2005



Tool Holder and Base – Model 2217

- Firmly holds rotary tools in any position.
- Control workpiece (hands free) for better results.



400 398 395 285 275 800 780 770 750

.

400 398 395 285 275 800 780 770 750


NEW!

. . . .

Right Angle Attachment – Model 575

Enhances the versatility of your Dremel rotary tool by allowing you to get into hard-to-reach areas.

- Ball bearings and spiral bevel gears provide smooth and cool operation
- Coupling system allows you to orient the attachment on your tool in 12 different directions
- Quick connect system easily attaches to your rotary tool in place of the housing cap, no wrenches required
- Compact, durable design for those "hard-toreach" places



Lawn Mower and Garden Tool Sharpener – Model 675

The fastest, easiest, safest way to sharpen your lawn mower blade and other garden tools.

- Guide provides optimum sharpening angle.
- Sharpens most rotary lawn mower blades.
- Easy to install and use.
- Long-wearing ABS plastic material.
- · Comfortable ergonomic design.
- Includes grinding stone, #932 (see p.29).



400 398 395 285 275 800 780 770 750

.

Chain Saw
Sharpening Attachment –

Model 1453

• Easily sharpen the dullest of chains.

Contents

- Sharpening attachment
- 3 Sharpening Stones Nos. 453, 454 and 455. (see p. 28) • Wrench • Instructi
- Gauge
- 2 Spacers
 - Instruction manual



DREMELiteTM – Model 677

The new attachment that lights your way!

- Provides visibility in dimly lit areas and increases light on detailed projects.
- Easy to attach, no confusing wires or connections.
- Two extremely long lasting and durable LED lights.
- Uses a magnet threaded onto the tool's output shaft to provide a clever and simple power source.





TOOLS NOT INCLUDED WITH ATTACHMENTS

22

Attachments



Flex Shaft Attachment -Model 225

Ideal for hard to reach places and fine detail work.

- · Quick connect attach system.
- 36" long cable with new 5" bend radius provides more flexibility.
- · Comfort grip hand piece.
- Integrated shaft lock button.
- Holds up to 1/8" shank.
- · Works with collet system and Dremel chuck.

Holder - Model 2222



400 398 395 285 275 800 780 770 750

. . . .


Flex Shaft Tool

Conveniently suspends any Dremel Rotary Tool above your workbench.

- Perfect for use with the Flex-Shaft attachment.
- Clamps to workbenches up to 1-3/4" thick, and adjusts in height from 12" to 42".
- Store extra bits on base.







Shaper/Router Table -

400 398 395 285 275 800 780 770 750

Converts your corded Rotary Tool into a bench mounted wood shaper.

 Features an adjustable fence and large 8" x 6" worktable.

Model 231

· Slot, groove, sand and trim edges.





400 398 395 285 275 800 780 770 750

Attachments

Mini Saw

Attachment - Model 670

Works great on wood and all wood-like materials.

- Quick connect system attaches to your rotary tool in seconds.
- Make clean, straight perpendicular cuts up to 1/4" thick.
- Clear housing provides better visibility.
- Lower guard retracts when not in use to ensure safety.
- Includes blade 546 shown below.





Rip/Crosscut Blade - Model 546

- Long-lasting steel blade.
- 1-1/4" diameter, 48 teeth.
- One blade per package.
- For use with Mini Saw Attachment only.

Miscellaneous Attachments



Foot Speed Control - Model 221

- Pressure sensitive pedal provides speed control.
- Variable speed from 0 to full RPM.
- 6 Amp. capacity.
- Use only with single speed rotary tools 275 and 732.



D-Vise -**Model 2214**

- Vise swivels 360° and tilts 180° in all directions.
- Padded jaws open to 2-1/2".



Deluxe Window Storage Case - Model 2610999673

Accessories not included.



Tool Storage Case - Model 15009 Model 90962



Wrench -

 For ease of changing bits

TOOLS NOT INCLUDED WITH ATTACHMENTS

24

Carving/Engraving

HIGH SPEED CUTTERS High speed cutters can be used for shaping, hollowing, grooving, slotting, making tapered holes in soft metals, plastics and woods. No. 199 cutter can be used to make small slits.








ENGRAVING CUTTERS Quality cutters for detail engraving, carving, routing in wood, fiberglass, plastic and soft metals.





DIAMOND WHEEL POINTS For fine detail work, engraving, carving, touch-up and finishing. Use on wood, jade, ceramic, glass, hardened steel, semi precious stones and other hard materials. Bits are covered with diamond particles.



7150 - Dual Package which includes 1 ea. 7103 and 7144



STRUCTURED TOOTH TUNGSTEN CARBIDE CUTTERS

Fast cutting sharp teeth for greater material removal. Use on fiberglass, wood, plastic, epoxy, rubber, laminates, particle board and ceramic tile.





TUNGSTEN CARBIDE CUTTERS Use for shaping, smoothing and material removal. Use on hardened steel, stainless steel, cast iron, nonferrous metals, fired ceramics, plastics, hardwoods and other hard materials. Not for use with floor tile.





Routing

ROUTER BITS For routing, inlaying, and mortising in wood and other soft materials. Use with Dremel No. 330 Router Attachment, No. 335 Plunge Router Attachment, and No. 231 Shaper/Router Table. Made of high speed steel.






Grinding/Sharpening

SILICON CARBIDE GRINDING STONES (BLUE / GREEN)

Designed to work well on stone, glass, ceramics, porcelain and non-ferrous metals.





CHAIN SAW SHARPENING STONES Precision ground for quick, easy sharpening of chain saw blades. Each package

contains 2 stones.






Grinding/Sharpening (Continued)

Accessories

ALUMINUM OXIDE GRINDING STONES (ORANGE / BROWN)


Use on metals, castings, welded joints, rivets and rust. Ideal for sharpening, de-burring and general purpose grinding of most materials.






ALUMINUM OXIDE ABRASIVE WHEEL

Perfect for cleaning, de-burring, removing rust, and polishing of most metals, including stainless steel.



ALUMINUM OXIDE GRINDING WHEEL Use for de-burring, rust

wheel Use for de-burring, rus removal and general purpose grinding.



ABRASIVE POINTS

Abrasive points are great for finishing work and light de-burring. They can be used



for paint and rust removal without removing any of the base material.



28

DRYWALL, MULTIPURPOSE, TILE AND **GROUT ACCESSORIES**

Drvwall Cutting Bit - Model 560*

Gives you fast clean cuts in drywall.

Multipurpose Cutting Bit - Model 561*

Cuts hardwood up to 3/8" and softwood up to 5/8". Also cuts plastic, fiberglass, drywall, laminate, aluminum & vinyl siding.

Tile Cutting Bit -Model 562*

Cuts ceramic wall tile. cement board, and plaster. (Not for use on floor tile.)

Carbide Grout Removal Bits - Model 569 and Model 570[†]

Ideal for replacing wall and floor grout or removing grout to replace broken tiles.

*Use with cutting guide (page 21) † Use with grout removal guide (page 20)

RIP/CROSSCUT BLADE -Model 546

For use with Mini Saw Attachment #670 only (page 22). Thickness .023" (0,6 mm)

DIAMOND WHEEL - Model 545

Great for cutting, sawing and carving of hard materials such as marble, concrete, brick, porcelain, ceramics, hard epoxy, soft and hard wood. Mandrel #402 is included. Thickness .023" (0,6 mm)


















CUT-OFF WHEELS

For slicing and cutting metal, wood and plastic. Cut-Off Wheels make it easy to cut or slot bolts, screws, sheet metal, thin wood and plastic. The cut-off wheel cuts only along its edge. Do not attempt to sand or cut curved holes with them.






540 with Mandrel 402



FIBERGLASS REINFORCED CUT-OFF WHEELS





456 package includes 10 Cut-Off Wheels and a washer set. Washer set only used with 456. Mandrel #402 is sold separately.



426A

12 per pack

CUTTING/SHAPING WHEEL Model 542 (CARBIDE)

20 per pack

For cutting and shaping on soft and hard woods, fiberglass, plastics and laminates. Do not use on metal. Mandrel included. Thickness .070" (1,8 mm)


542



Cleaning/Polishing

RUBBER POLISHING POINTS - Blue points for finishing and polishing all ferrous metals. Removes small burrs and scratch marks left by grinding and sanding, and cleans and defines grooves. Also effective on many stones and ceramics.







Use 414.

422 and

Use 425

Mandrel

with


402

POLISHING ACCESSORIES

Cloth 1" dia.

Ideal for polishing metals and plastics. Using polishing compound No. 421 with wheels produces a high luster.







1/4"

6,4 mm

463











429



POLISHING COMPOUND - Model 421

Use with felt or cloth accessories to polish metals and plastics. Compound will remove a dull oxidized film and/or light surface imperfections. A solid compound.



POLISHING WHEEL - Model 520

Use for light stock removal and high luster polishing of metals and hard plastics. The wheel is impregnated with a silicon carbide abrasive and lubricant, eliminating the need for polishing compound.





ABRASIVE BRUSH - Model 538

Dremel's strongest and longest lasting brush. Extra-thick nylon bristles are coated with an abrasive grit for material removal on the toughest jobs. Use for de-burring metal or wood and for removing rust and paint.



Do not run brush in excess of 20,000 RPM.



cleaning, polishing of silverware, jewelry and other precious metals; can use with polishing compound.

CARBON STEEL BRUSHES





3/4"

19,1 mm

428

3/4"

19,1 mm

530

3/4"










12,7 mm

531

1/2"







532



Stainless steel brushes do not cause "after-rust" when used on corrosive-resistant materials like pewter. aluminum and stainless steel









BRASS BRUSHES 3,2 mm Brass brushes are nonsparking and softer than steel. They will not scratch soft metals like gold, copper, brass.

Do not run brushes in excess of 15.000 RPM.



32