

T8 Luxline Plus Special Length

F36W/1M/T8/840
0001504

Product features



PRODUCT OVERVIEW

Product name	F36W/1M/T8/840
Technology	Fluorescent
Watt (Rated) (W)	36.00
Lamp shape	Tube, double-ended
Type	T8 Luxline Plus Special Length
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Retail, Residential & Consumer
ETIM Class	EC000108
E-number FI	4940734
E-number SE	8356800
Luminous flux (lm)	3100
Colour temperature (K)	4000
Light colour	Cool White
Colour Code	840
CRI (Ra)	85
Colour Variation Initial (SDCM)	SDCM5
Photobiological Risk Group	Not applicable
Wattage (W)	36.00
Product Voltage (V)	80
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Average life (Nominal) (h)	20000
Product EAN number	5410288015040

DATA TABLE

General data

Product name	F36W/1M/T8/840
Technology	Fluorescent
Watt (Rated) (W)	36.00

T8 Luxline Plus Special Length

F36W/1M/T8/840

0001504

Lamp shape	Tube, double-ended
Type	T8 Luxline Plus Special Length
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Retail, Residential & Consumer
ETIM Class	EC000108
E-number FI	4940734
E-number SE	8356800

Optical data

Luminous flux (lm)	3100
Luminous flux (Rated) (lm)	3100
Ambient temperature for maximum luminous flux (°C)	25
Colour temperature (K)	4000
Light colour	Cool White
Colour Code	840
CRI (Ra)	85
Colour Variation Initial (SDCM)	SDCM5
Adjustable chromaticity	N
Photobiological Risk Group	Not applicable
Rated lumen maint. factor (%) at 2000 h 50Hz	0.96
Rated lumen maint. factor (%) at 4000 h 50Hz	0.94
Rated lumen maint. factor (%) at 6000 h 50Hz	0.92
Rated lumen maint. factor (%) at 8000 h 50Hz	0.91
Rated lumen maint. factor (%) at 12000 h 50Hz	0.90
Rated lumen maint. factor (%) at 16000 h 50Hz	0.89
Rated lumen maint. factor (%) at 20000 h 50Hz	0.87

Electrical data

Wattage (W)	36.00
Current (A)	0.56
Product Voltage (V)	80
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Drive current (mA)	560
Lamp Energy Label (class)	G
kWh per 1000 hours burning time	43
Nominal Frequency (Hz)	50Hz

T8 Luxline Plus Special Length

F36W/1M/T8/840

0001504

Lifetime data

Average life (Nominal) (h)	20000
Average life (Rated) (h)	20000
Rated survival factor (%) at 2000 h 50Hz	0.99
Rated survival factor (%) at 4000 h 50Hz	0.98
Rated survival factor (%) at 6000 h 50Hz	0.96
Rated survival factor (%) at 8000 h 50Hz	0.94
Rated survival factor (%) at 12000 h 50Hz	0.92
Rated survival factor (%) at 16000 h 50Hz	0.80
Rated survival factor (%) at 20000 h 50Hz	0.50

Physical data

Nominal Product Length (mm)	970.0
Nominal Product Diameter (mm)	26
Max. Length base to base (mm) - A	970.0
Length base to pin Min-Max (mm) - B	974.7-977.1
Max. Lamp Length (mm) - C/L	984.2
Max. Lamp Diameter (mm) - D	28.0
Weight (kg)	0.131

Packaging


Single packaging type	Carton
Product EAN number	5410288015040
Packaging single length / height (cm)	98.5
Packaging single width (cm)	2.9
Packaging single depth (cm)	2.8
DUN14 (outer)	15410288015047
Units per outer package	25
Packaging outer length / height (cm)	104.0
Packaging outer width (cm)	15.5
Packaging outer depth (cm)	15.0

Safety data

Lamp mercury content (mg)	2.80
Breakage cleaning instructions	Applicable
Recommendation for disposal at end of life	Applicable
Special purpose lamp	Yes
Suitable for household illumination	Yes

PHOTOMETRY

T8 Luxline Plus Special Length F36W/1M/T8/840 0001504



TECHNICAL DRAWINGS



0001504



36
kWh/1000h



2019/2015

SYLVANIA


T8 Luxline Plus Special Length

F36W/1M/T8/840

0001504



0001504



36
kWh/1000h



2019/2015