



SCALANCE XC206-2G PoE Manageable Layer 2 IE PoE Switch; IEC 62443-4-2 certified; 6x 10/100/1000 Mbps RJ45 PoE ports acc. to IEEE802.3at; 2 ports of which according to IEEE802.3bt ; 2x 1,000, 10,000 Mbps SFP+; PoE support for 54 V DC Infeed; 240 W PoE Power can be distributed among all ports; 1x console port; diagnostics LED; redundant power supply; temperature range -40 °C to +60 °C; mounting on DIN rail/S7 mounting rail /wall; Redundancy functions; Office features (RSTP, VLAN,...); PROFINET device; Ethernet/IP-compliant; C-PLUG slot; IEEE 1588v2 PTP

product type designation	SCALANCE
transfer rate	
transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s, 10 Gbit/s
interfaces / for communication / maximum configuration for modular devices	
number of electrical ports / maximum	6
number of electrical ports / with PoE / maximum	6
number of optical ports / maximum	2
interfaces / for communication / integrated	
number of electrical connections	6; RJ45
<ul style="list-style-type: none"> for network components or terminal equipment 	
number of 10/100/1000 Mbit/s RJ45 ports / integrated	4 PoE ports according to IEEE 802.3at (30 W), 2 PoE ports according to IEEE 802.3bt (60 W)
<ul style="list-style-type: none"> with securing collar 	
<ul style="list-style-type: none"> with securing collar / with PoE 	6
number of electrical connections	
<ul style="list-style-type: none"> for SFP 	2
interfaces / for communication / plug-in	
number of electrical connections	
<ul style="list-style-type: none"> for SFP+ 	2; SFPs with 1000 Mbps or 10,000 Mbps possible; 100 Mbps with SFP991-1(LD) A possible
interfaces / other	
number of electrical connections	
<ul style="list-style-type: none"> for operator console 	1
<ul style="list-style-type: none"> for signaling contact 	1
type of electrical connection	
<ul style="list-style-type: none"> for operator console 	RJ11
<ul style="list-style-type: none"> for signaling contact 	2-pole terminal block
<ul style="list-style-type: none"> for power supply 	4-pole terminal block
design of the removable storage	
<ul style="list-style-type: none"> C-PLUG 	Yes
signal inputs/outputs	
operating voltage / of the signaling contacts	
<ul style="list-style-type: none"> at DC / rated value 	54 V
operational current / of the signaling contacts	
<ul style="list-style-type: none"> at DC / maximum 	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
supplied active power / of PSE / with PoE	
<ul style="list-style-type: none"> total / maximum 	260 W
type of voltage / 1 / of the supply voltage	DC

<ul style="list-style-type: none"> • supply voltage / 1 / rated value 	54 V
<ul style="list-style-type: none"> • power loss [W] / 1 / rated value 	10 W
<ul style="list-style-type: none"> • supply voltage / 1 / rated value 	52 ... 57 V
<ul style="list-style-type: none"> • consumed current / 1 / maximum 	5 A
<ul style="list-style-type: none"> • product component / 1 / fusing at power supply input 	Yes
<ul style="list-style-type: none"> • fuse protection type / 1 / at input for supply voltage 	15 A / 125 V
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> • during operation 	-40 ... +60 °C
<ul style="list-style-type: none"> • during storage 	-40 ... +85 °C
<ul style="list-style-type: none"> • during transport 	-40 ... +85 °C
<ul style="list-style-type: none"> • note 	installation position and SFPs used during the operation have to be considered (see manual)
relative humidity	
<ul style="list-style-type: none"> • at 25 °C / without condensation / during operation / maximum 	95 %
protection class IP	IP20
design, dimensions and weights	
design	compact
width	60 mm
height	147 mm
depth	125 mm
net weight	0.54 kg
product feature / conformal coating	No
material / of the enclosure	Polycarbonate (PC-GF10) / pressure die cast aluminum
fastening method	
<ul style="list-style-type: none"> • 35 mm top hat DIN rail mounting 	Yes
<ul style="list-style-type: none"> • wall mounting 	Yes
<ul style="list-style-type: none"> • S7-300 rail mounting 	Yes
<ul style="list-style-type: none"> • S7-1500 rail mounting 	Yes
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of $\leq 0.3\text{ s}$	50
cascading in cases of star topology	any (depending only on signal propagation time)
product function / QoS according to DSCP	Yes
product feature	
<ul style="list-style-type: none"> • Cut Through switching method 	No
<ul style="list-style-type: none"> • Store & Forward switching method 	Yes
product functions / management, configuration, engineering	
product function	
<ul style="list-style-type: none"> • CLI 	Yes
<ul style="list-style-type: none"> • web-based management 	Yes
<ul style="list-style-type: none"> • MIB support 	Yes
<ul style="list-style-type: none"> • TRAPs via email 	Yes
<ul style="list-style-type: none"> • configuration with STEP 7 	Yes
<ul style="list-style-type: none"> • RMON 	Yes
<ul style="list-style-type: none"> • SMTP server 	No
<ul style="list-style-type: none"> • port mirroring 	Yes
<ul style="list-style-type: none"> • multipoint mirroring 	Yes
<ul style="list-style-type: none"> • CoS 	Yes
<ul style="list-style-type: none"> • PROFINET IO diagnosis 	Yes
PROFINET conformity class	B
network load class / according to PROFINET	3
product function / switch-managed	Yes
telegram length / for Ethernet / maximum	10240 byte
protocol / is supported	
<ul style="list-style-type: none"> • Telnet 	Yes
<ul style="list-style-type: none"> • HTTP 	Yes
<ul style="list-style-type: none"> • HTTPS 	Yes
<ul style="list-style-type: none"> • TFTP 	Yes
<ul style="list-style-type: none"> • BOOTP 	No

• GMRP	Yes
• DCP	Yes
• LLDP	Yes
• EtherNet/IP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
protocol / is supported / GVRP	Yes
product functions / DHCP	
product function	
• DHCP server	Yes
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
product functions / redundancy	
product function	
• of the PROFINET IO device / is supported / PROFINET system redundancy	Yes
• ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• Media Redundancy Protocol Interconnection (MRP-I)	Yes
• of the PROFINET IO device / is supported / H-Sync forwarding	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure RSTP+	Yes
• redundancy procedure MSTP	Yes
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• passive listening	Yes
protocol / is supported	
• LACP	Yes

product functions / security	
product function	
• IEEE 802.1x (radius)	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	
• SSH	Yes
• SSL	Yes
product functions / time	
product function	
• SICLOCK support	Yes
• NTP-client	Yes
• SNTP client	Yes
protocol / is supported	
• NTP	Yes
• SNTP	Yes
• IEEE 1588 profile default	Yes
system modification during operation	
product function / configuration in RUN via CiR/H-CiR	Yes
standards, specifications, approvals	
standard	
• for emitted interference	EN 61000-6-4:2001 (Class A)
• for interference immunity	EN 61000-6-2:2001
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
MTBF	37 a
reference code	
• according to IEC 81346-2	KF
• according to IEC 81346-2:2019	KFE
standards, specifications, approvals / CE	
certificate of suitability / CE marking	Yes
product conformity / according to EMC-guideline	2014/30/EU
standard	
• for EMC interference emission	EN 61000-6-4, EN 50121-15
• for immunity to EMC	EN 61000-6-2, EN 50121-4
certificate of suitability / RoHS conformity	Yes; 2011/65/EU
standards, specifications, approvals / hazardous environments	
certificate of suitability	
• ATEX	Yes
• for ATEX / as marking	II 3 G Ex ec IIC T4 Gc
• IECEx	Yes
• for IECEx / as marking	Ex ec IIC T4 Gc
• CCC / for hazardous zone according to GB standard	Yes
• CCC / for hazardous zone according to GB standard / as marking	Ex nA IIC T4 Gc
• for cULus HazLoc / as marking	CL1, DIV2, Group A,B,C,D T4, CL1, Zone 2, Group IIC, T4
• FM registration	Yes; FM Class 3600:2018, FM Class 3611:2021, FM Class 3810:2021, ANSI/UL 121201:2017, ANSI/UL 61010-1:2018
• for FM / as marking	CL1, DIV2, group A,B,C,D T4, CL1, Zone 2, group IIC, T4 Ta: -40 °C +70 °C
standards, specifications, approvals / other	
certificate of suitability	
• KC approval	Yes
• railway application in accordance with EN 50121-4	Yes
• Regulatory Compliance Mark (RCM)	Yes
• for UL 61010-2-201 / as File Nr.	E85972 (NRAQ, NRAQ7)
• EAC approval	Yes
accessories	
product extension / optional / C-PLUG	Yes
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool

- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx-Download-Manager
- to website: Industry Online Support

- <http://www.siemens.com/simatic-net>
- <https://mall.industry.siemens.com>
- <http://www.siemens.com/industry/infocenter>
- <http://automation.siemens.com/bilddb>
- <http://www.siemens.com/cax>
- <https://support.industry.siemens.com>

security information

security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

5/27/2023 