

CPF0805B665KE ✓ ACTIVE

TE Internal #: 7-1614889-8

Surface Mount Resistors, Precision Resistor, 2 Termination, 0805, Reel, .1 %, Thin Film, Resistance Class 1k Ω – 1M Ω , 665K Ω , .1 W, ± 25 ppm/ $^{\circ}$ C, Solder

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Number of Terminations: **2**

Package Size Code: **0805**

Packaging Method: **Reel**

Passive Component Tolerance: **.1 %**

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Precision Resistor
Package Size Code	0805
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Voltage Rating	100 V
Passive Component Tolerance	.1 %
Resistance Class	1k Ω – 1M Ω
Resistance Value	665K Ω
Power Rating	.1 W

Termination Features

Number of Terminations	2
------------------------	---



Surface Mount Resistor Termination Type Solder

Dimensions

Passive Component Dimensions 2 x 1.25 x .5 mm

Usage Conditions

Operating Temperature Range -55 – 155 °C

Temperature Coefficient ±25 ppm/°C

Packaging Features

Packaging Method Reel

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU Compliant

EU ELV Directive 2000/53/EC Compliant

China RoHS 2 Directive MIIT Order No 32, 2016 No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006
 Current ECHA Candidate List: JUNE 2022 (224)
 Candidate List Declared Against: JUNE 2022 (224)
 Does not contain REACH SVHC

Halogen Content Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1614889-8
CPF 0805 102K 0.1% 25PPM 5K RL



TE Part # 1614889-9
CPF 0805 105K 0.1% 25PPM 5K RL



TE Part # 1-1614889-0
CPF 0805 107K 0.1% 25PPM 5K RL



TE Part # 1-1614889-1
CPF 0805 113K 0.1% 25PPM 5K RL



TE Part # 1-1614889-2
CPF 0805 115K 0.1% 25PPM 5K RL



TE Part # 1-1614889-3
CPF 0805 118K 0.1% 25PPM 5K RL



TE Part # 1-1614889-4
CPF 0805 121K 0.1% 25PPM 5K RL



TE Part # 1-1614889-5
CPF 0805 124K 0.1% 25PPM 5K RL



TE Part # 1-1614889-6
CPF 0805 127K 0.1% 25PPM 5K RL



TE Part # 1-1614889-7
CPF 0805 133K 0.1% 25PPM 5K RL



TE Part # 1-1614889-8
CPF 0805 137K 0.1% 25PPM 5K RL



TE Part # 1-1614889-9
CPF 0805 140K 0.1% 25PPM 5K RL



TE Part # 2-1614889-0
CPF 0805 143K 0.1% 25PPM 5K RL



TE Part # 2-1614889-1
CPF 0805 147K 0.1% 25PPM 5K RL



TE Part # 2-1614889-2
CPF 0805 154K 0.1% 25PPM 5K RL



TE Part # 2-1614889-3
CPF 0805 158K 0.1% 25PPM 5K RL



TE Part # 2-1614889-4
CPF 0805 162K 0.1% 25PPM 5K RL



TE Part # 2-1614889-5
CPF 0805 165K 0.1% 25PPM 5K RL



TE Part # 2-1614889-6
CPF 0805 169K 0.1% 25PPM 5K RL



TE Part # 2-1614889-7
CPF 0805 174K 0.1% 25PPM 5K RL

Documents

Product Drawings

[CPF 0805 665K 0.1% 25PPM 5K RL](#)



English

[Datasheets & Catalog Pages](#)

[CPF-1016](#)

English