




ITEM	COMPONENT	MATERIAL	FINISH
1	REC SHELL	BRASS	NICKEL PLATED
2	INSERT	PUR	BLACK
3	CONTACT	BRASS / GOLD	CuZn Ni/ Au
4	M16 NUT	BRASS	NICKEL PLATED
5	O-RING	NBR	BLACK
6	O-RING	VITON	RED
7	POTTING MATERIAL	WEVO	NONE



POL MATERIAL NO. ENGINEERING NO.
8 1200840033 WR8U40000

VOLTAGE RATING: 30 VAC / 36 VDC
 AMPERAGE RATING: 2 A
 PROTECTION CLASS: IP 67/68/69K
 OPERATING TEMPERATURE: -25°C / 90°C
 UL CERTIFICATION: FILE NO. E152210
 CSA CERTIFICATIONS: FILE NO. LR6837

ENTER DESCRIPTION EC NO: IFG2014-0351 DRW: BBAUCH 2013/09/26 CH: KD-APÖHL 2013/10/16 APPR: CBÜRGER 2014/01/31 REV 2	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.05 ± --- 1 PLACE ± 0.1 ± --- 0 PLACE ± 0.2 ± --- ANGULAR ± 1 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE MM ONLY DRAWN BY: NSTAUDIGEL DATE: 2010/01/26 CHECKED BY: _____ DATE: _____ APPROVED BY: FPACHER DATE: 2010/02/01 MATERIAL NO. see table	SCALE 4:1 DESIGN UNITS METRIC THIRD ANGLE PROJECTION	TITLE REC U12 8P AC FE STR PUR M16 BM WIR SE SHLD BRA AU molex DOCUMENT NO. SD-120084-017	SHEET NO. 1 OF 1
	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
	SIZE A3					
	POL MATERIAL NO. ENGINEERING NO. 8 1200840033 WR8U40000					