

Industrial Ethernet IE-SW-VL05M-5TX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Product image



The Value Line from Weidmüller consists of unmanaged and managed switches in a high-quality IP 30 protected metal housing. The equipment can be delivered with Fast Ethernet and Gigabit Ethernet ports. Value Line managed switches support a variety of helpful management functions, such as fast ring redundancy, port-based VLAN, QoS, RMON, bandwidth management, port mirroring and error notification via e-mail or a relay. The ring redundancy can be simply set via the web based management interface, or with a dip switch found on the top of the switch.

- Unmanaged Plug & Play switches in a high-quality metal housing (IP 30)
- Price-conscious middle-range
- Managed switches for the entry into a configurable network infrastructure
- Unmanaged full Gigabit switch with 8 ports
- Approvals: CE, FCC, cULus, Class I Div. 2 / ATEX, DNV / GL

General ordering data

Type	IE-SW-VL05M-5TX
Order No.	1504280000
Version	Network switch, managed, Fast Ethernet, Number of ports: 5x RJ45, IP30, -10 °C...60 °C
GTIN (EAN)	4050118312256
Qty.	1 pc(s).

**Industrial Ethernet
IE-SW-VL05M-5TX**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	53.6 mm	Width (inches)	2.11 inch
Height	135 mm	Height (inches)	5.315 inch
Depth	105 mm	Depth (inches)	4.134 inch
Net weight	650 g		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

EMC conformity and approvals

EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 GHz: 20 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 1 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 2 kV, IEC 61000-4-6 CS: 10 V, IEC 61000-4-8	Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D
Free fall	According to IEC 60068-2-32	Ship use	DNV-GL
Shock	according to IEC 60068-2-27	Vibration	according to IEC 60068-2-6

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	60 °C
Operating temperature, min.	-10 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Guarantee

Time interval 5 years

Interfaces

Alarm contact	1 relay output with a current capacity of 1 A at 24 V DC	Console port interface	RS-232
DIP switch	Turbo-Ring, Master, Coupler, Reserve	LED indicator	PWR1, PWR2, FAULT, MSTR/HEAD, CPLR/TAIL, 10/100M (TP-Port)
Number of ports	5x RJ45	RJ45 ports	10/100BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port

MTBF

MTBF	1,547,941 hrs	Database	Telcordia (Bellcore), GB
------	---------------	----------	--------------------------

**Industrial Ethernet
IE-SW-VL05M-5TX**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Power supply**

Connection type	1 removable 6-pin terminal block		
Current consumption	Voltage	24 V DC	
	Current	0.286 A	
Overload current protection	Existing		
Reverse polarity protection	Available		
Voltage supply	12/24/48 V DC, 2 redundant inputs		

Switch characteristics

Bandwidth backplane	1 Gbps	IGMP-Groups	256
MAC table size	2 K	Max. number of available VLANs	64
Packet buffer size	1 Mbit	Priority queues	4
VLAN-ID max	4,094	VLAN-ID min	1

Technical data

Housing main material	metal	Protection degree	IP30
Type of mounting	DIN rail, Panel (with optional mounting kit)		

Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
MIB	MIB-II, Ethernet-Like MIB, P-BRIDGE MIB, Bridge MIB, RSTP MIB, RMON MIB Group 1, 2, 3, 9	Protocol	IGMPv1/v2, GMRP, GVRP, SNMPv1/v2c/v3, DHCP Server/Client, TFTP, SNTP, SMTP, RARP, RMON, HTTP, Telnet, Syslog, DHCP option 66/67/82, BootP, LLDP, PROFINET, EtherNet/IP, Modbus/TCP, IPv6
Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X), IEEE 802.3x for flow control, IEEE 802.1D-2004 for the Spanning Tree protocol, IEEE 802.1w for Rapid STP, IEEE 802.1p for Class of Service, IEEE 802.1Q for VLAN tagging		

Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
eClass 9.0	19-17-01-06	eClass 9.1	19-17-01-06
eClass 10.0	19-17-04-01		

Data sheet

**Industrial Ethernet
IE-SW-VL05M-5TX**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	ODVA Certificate PNO Certificate DNV-GL certificate KC certificate EU Declaration of Conformity
Brochure/Catalogue	CAT 9 IETH 18/19 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
Product Change Notification	Firmware Release Notes Product Change Notification IE-SW-VL05M-series
Software	SNMP MIB file GSDML IE-SW-VL05M-series EDS IE-SW-VL05M-series Managed Switch Configuration Utility Firmware Version 3.6.24
User Documentation	Hardware Installation Guide Manual 20191204 Security Advisory IE Managed Switches