


# ME5015



## Magnetic sensor

MEB3060-ANKG/PH



### Product characteristics

Electrical design	NPN
Output function	normally open
Sensing range [mm]	60; (referred to magnet M 4.0)
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 40

### Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10
Protection class	III
Reverse polarity protection	yes

### Outputs

Electrical design	NPN
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	5000
Short-circuit protection	yes
Overload protection	yes

### Detection zone

Sensing range [mm]	60; (referred to magnet M 4.0)
--------------------	--------------------------------

### Accuracy / deviations

Hysteresis [% of Sr]	1...10
----------------------	--------

### Operating conditions

Ambient temperature [°C]	-25...75
Protection	IP 67

# ME5015



## Magnetic sensor

MEB3060-ANKG/PH

### Tests / approvals

EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
MTTF	[years]	2028

### Mechanical data

Weight	[g]	69
Housing		threaded type
Dimensions	[mm]	M8 x 1 / L = 40
Thread designation		M8 x 1
Materials		housing: stainless steel (1.4404 / 316L); sensing face: PBT orange; end cap: PA; lock nuts: brass

### Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

### Accessories

Accessories (supplied)	lock nuts: 2
------------------------	--------------


### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection

Cable: 2 m, PUR / PVC; 3 x 0.14 mm<sup>2</sup>

### Connection



Core colours :

- BK = black
- BN = brown
- BU = blue