Electrolytic Capacitor MCMHR Series

multicomp PRO





Features

- Developed short body length to 7mm, for the demand of smaller and thinner electronic equipment
- Most suitable for high-density electronic equipment, such as, automatic office machines, pocket calculators, car stereos and mini-audio sets, VCR, camera, CD-ROM, notebook

Specifications

Item	Performance										
Operating Temperature Range	-40°C to +105°C										
Rated Working Voltage Range		6.3V DC to 63V DC									
Nominal Capacitance Range					0.1µF 1	to 470µF	=				
Capacitance Tolerance			=	±20	% (at+2	20°C,120) Hz)				
Leakage Current		=	0.01	CV	or 3 (µ	A) after	two min	lutes			
Dissipation Factor (Tan δ)		Working Voltage (V)	6.3	3	10	16	25	35	50	63]
(120Hz\+20°C)		Tan δ Max.	0.2	4	0.2	0.16	0.14	0.12	0.1	0.08]
Characteristics at Low Temperature (stability at 120Hz)	Γ	Working Voltage (V)	6.3	3	10	16	25	35	50	63	
	[-25°C /+ 20°C	4		3	2	2	2	2	2]
		-40°C /+ 20°C	8		6	4	3	3	3	3]
High Temperature Loading	After 1,000 hours application of DC rated working voltage at +105°C, The capacitor shall meet the following limits: Post test requirements at +20°C Leakage Current ≤ The initial specified value Capacitance change ≤ ±20% of initial specified value										
	Dissipation Factor (Tan δ) \leq 200% of initial specified value										
Shelf Life	After storage for 500 hours at +105°C with no voltage applied Post test requirements at +20°C same limits as high temperature loading										
Solvent Proof	This capacitor can withstand circuit-board cleaning within 5 min. dipped in Freon TE, TES at 40°C (ultrasonic also permitted) or in the steam of these cleaners										


Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




Electrolytic Capacitor MCMHR Series

multicomp PRO

Diagram





ØD (+0.5 Maximum)	3	4	5	6.3	8
F (±0.5)	1	1.5	2	2.5	3.5
Ød (±0.02)	0.4	0.45	0.45	0.45	0.5

Case Size Table

ØD × L (mm)

₩.V. (SV) μF	6.3 (8)	10 (13)	16 (20)	25 (32)	35 (44)	50 (63)	63 (79)	
0.1	-	-	-	-	()	(()	
0.22	-	-	-	-	1			
0.33	-	-	-	-	1		4 × 7	
0.47	-	-	-	-	R	4 × 7		
1	-	-	-	-				
2.2	-	-	-	-				
3.3	-	-	-	-				
4.7	-	-	R	4 × 7	4 × 7	5 × 7	5 × 7	
10	-	R	4 × 7	5 × 7	5 × 7	6.3 × 7	6.3 × 7	
22	4 × 7	5×7	5 × 7		6.3 × 7	0.3 ^ 7	-	
33	5 × 7	5.7		6.3 × 7	0.3 ~ 7	8 × 7	-	
47	5 ~ 7	6.3 × 7	6.3 × 7	6.3 × 7		8 × 7	8 × 9	-
100	6.3 × 7	0.3 ^ /		8 × 9	-	-	-	
220	8 × 7	8 × 7	8 × 9	-	-	-	-	
330	0 ^ /	0^/	0^9	-	-	-	-	
470	8 × 9	8 × 9	-	-	-	-	-	

All blank voltage on sleeve marking is the same voltage as "R" point to.

Part Number Table

Description	Part Number
Capacitor, 22µF, 6.3V	MCMHR6V3226M4X7
Capacitor, 33µF, 6.3V	MCMHR6V3336M5X7
Capacitor, 47µF, 6.3V	MCMHR6V3476M5X7
Capacitor, 100µF, 6.3V	MCMHR6V3107M6.3X7

Description	Part Number			
Capacitor, 220µF, 6.3V	MCMHR6V3227M8X7			
Capacitor, 470µF, 6.3V	MCMHR6V3477M8X7			
Capacitor, 22µF, 10V	MCMHR10V226M5X7			
Capacitor, 33µF, 10V	MCMHR10V336M5X7			

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



multicomp PRO

Description	Part Number
Capacitor, 47µF, 10V	MCMHR10V476M5X7
Capacitor, 100µF, 10V	MCMHR10V107M5X7
Capacitor, 220µF, 10V	MCMHR10V227M8X7
Capacitor, 330µF, 10V	MCMHR10V337M8X7
Capacitor, 470µF, 10V	MCMHR10V477M8X7
Capacitor, 220µF, 16V	MCMHR16V227M8X7
Capacitor, 330µF, 16V	MCMHR16V337M8X7
Capacitor, 4.7µF, 25V	MCMHR25V475M4X7
Capacitor, 10µF, 25V	MCMHR25V106M5X7
Capacitor, 22µF, 25V	MCMHR25V226M6.3X7
Capacitor, 33µF, 25V	MCMHR25V336M6.3X7
Capacitor, 47µF, 25V	MCMHR25V476M6.3X7
Capacitor, 100µF, 25V	MCMHR25V107M8X7
Capacitor, 4.7µF, 35V	MCMHR35V475M4X7
Capacitor, 0.1µF, 50V	MCMHR50V104M4X7
Capacitor, 0.22µF, 50V	MCMHR50V224M4X7
Capacitor, 0.33µF, 50V	MCMHR50V334M4X7
Capacitor, 0.47µF, 50V	MCMHR50V474M4X7
Capacitor, 1µF, 50V	MCMHR50V105M4X7
Capacitor, 2.2µF, 50V	MCMHR50V225M4X7
Capacitor, 4.7µF, 50V	MCMHR50V475M5X7
Capacitor, 33µF, 50V	MCMHR50V336M8X7
Capacitor, 47µF, 50V	MCMHR50V476M8X7

Description	Part Number
Capacitor, 0.22µF, 63V	MCMHR63V224M4X7
Capacitor, 0.33µF, 63V	MCMHR63V334M4X7
Capacitor, 0.47µF, 63V	MCMHR63V474M4X7
Capacitor, 2.2µF, 63V	MCMHR63V225M4X7
Capacitor, 3.3µF, 63V	MCMHR63V335M4X7
Capacitor, 10µF, 63V	MCMHR63V106M6.3X7
Capacitor, 330µF, 6.3V	MCMHR6V3337M8X7
Capacitor, 10µF, 16V	MCMHR16V106M4X7
Capacitor, 22µF, 16V	MCMHR16V226M5X7
Capacitor, 33µF, 16V	MCMHR16V336M6.3X7
Capacitor, 47µF, 16V	MCMHR16V476M6.3X7
Capacitor, 100µF, 16V	MCMHR16V107M6.3X7
Capacitor, 10µF, 35V	MCMHR35V106M5X7
Capacitor, 22µF, 35V	MCMHR35V226M6.3X7
Capacitor, 33µF, 35V	MCMHR35V336M6.3X7
Capacitor, 47µF, 35V	MCMHR35V476M8X7
Capacitor, 3.3µF, 50V	MCMHR50V335M4X7
Capacitor, 10µF, 50V	MCMHR50V106M6.3X7
Capacitor, 22µF, 50V	MCMHR50V226M6.3X7
Capacitor, 0.1µF, 63V	MCMHR63V104M4X7
Capacitor, 1µF, 63V	MCMHR63V105M4X7
Capacitor, 4.7µF, 63V	MCMHR63V475M5X7

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

