Explosion Proof Audible Signal - 115 dB (A)

Series YA90







- > Max sound output 115 dB (A) / 1 m
- > 2 stage alarm, independently selectable 2nd stage
- > IP66 rated as standard
- > 32 selectable tones meeting international regulations
- > Light weight glass reinforced polyester (GRP) Ex enclosure
- > Sound selection via 5 way DIL switch
- > Adjustable stainless steel ratchet bracket providing positive setting
- > Enclosure finished in red high performance paint with ABS flare
- > Monitoring facility (DC voltages only)
- > Dual 20 mm gland entries as standard











Directional audible signal designed for use in hazardous or harsh environments.

	ATEX / IECEx /				x /			NE	NEC 505 NEC 506					NEC 500						
	GOST				Class I					Cla		ss l	Clas	ss II	Clas	s III				
Zone	0	1	2	20	21	22	Zone	0	1	2	20	21	22	Division	1	2	1	2	1	2
For use in		Х	Х		Х	Х	For use in		Х	Х		Х	Х	For use in		Х		Х	Х	Х

Explosion Protection

Marking	
IECEx	
	YA90/B versions: Ex d IIB (Ta - 60 + 60 °C)
protection	YA90/C versions: Ex d IIC (Ta - 60 + 60 °C)
Dust explosion protection Europe (ATEX)	Ex tD A21 IP66 (Ta - 60 + 60 °C)
Gas explosion	YA90/B versions:
protection	YA90/C versions: 🔞 II G Ex d IIC (Ta - 60 + 60 °C)
Dust explosion protection	
Certificates	
IECEx	YA90/B versions: IECEx BAS 08.0062X
	YA90/C versions: IECEx BAS 08.0061X
Europe (ATEX)	YA90/B versions: Baseefa08ATEX0191X
	YA90/C versions: Baseefa08ATEX0189X
Other approvals	Brazil (INMETRO), Canada (ULC), China (CQST Ex), Russia (GOST-R), USA (UL)

WebCode YA90A

Explosion Proof Audible Signal - 115 dB (A)

Series YA90



_			_		
80	lecti	n	Тэ	h	Ω

Version	Group	Rated operational voltage	Order number	Art. no.	Weight		
YA90 Sounder.	IIC	24 V DC	YA90/C/D/EU	205209	kg 4.500		
ATEX certification,		115 V AC	YA90/C/L/EU	206770	4.500		
standard devices		230 V AC	YA90/C/N/EU	205214	4.500		
YA90 Sounder,	IIC	24 V DC	YA90/C/D/UL	205365	4.500		
UL certification,		115 V AC	YA90/C/L/UL	205366	4.500		
standard devices		230 V AC	YA90/C/N/UL	212397	4.500		
YA90 Sounder,	IIC	24 V DC	YA90/C/D/IN	205212	4.500		
IECEx certification,		115 V AC	YA90/C/L/IN	208871	4.500		
standard devices		230 V AC	YA90/C/N/IN	212398	4.500		
YA90 Sounder,	IIC	24 V DC	YA90/C/D/RU	206661	4.500		
GOST R certification,		115 V AC	YA90/C/L/RU	212399	4.500		
standard devices		230 V AC	YA90/C/N/RU	205217	4.500		
Note	Variations in gas group, voltage and certification are available Tag labels can be added, please contact your local sales office for more details						

Technical Data

Electrical data

Rated operational voltage


Current consumption

24, 48 V DC


115, 230 V AC 48 V DC (not available for UL listed products)


24 V DC, 300 mA 48 V DC, 160 mA 115 V AC, 80 mA 230 V AC, 45 mA

Schematic



AC alarm connections and sound signal selection





DC alarm connection and sound signal selection Legend

- = External power supply, provided by user
- = 24/48 or 0 V Input used for 2nd stage by supply reversal 19
- = Live voltage for sounder/horn, neutral voltage for sounder/horn, 22 switch for second stage alarm
- 23 = Connecting socket used for pressure unit
- = Dual in line sound selection switch 24
- 25 = Terminal blocks for incoming and outgoing wiring
- 27 = Connections to additional sounder/horn
- = Control voltage for sounder/horn, common voltage for sounder/horn, 28 switch for second stage alarm
- = Two stage alarm by third core, line monitoring by supply reversal, select alarm stage 1 on SW1, select alarm stage 2 on SW2
- = Two stage alarm by supply reversal, line monitoring by threshhold method (<1 V), select alarm stage 1 on SW1, select alarm stage 2 on SW2

Explosion Proof Audible Signal - 115 dB (A)

Series YA90






Technical Data						
Acoustic data						
Volume	115 db (A) / 1 m					
Sound selection	via DIL switch					
Ambient conditions						
Ambient temperature	ATEX / IECEx: - 60 + 60 °C UL & ULC: - 60 + 66 °C					
Max. relative humidity	95 % at 40 °C					
Mechanical data						
Material						
Enclosure	light weight glass reinforced polyester (GRP) enclosure finished in red high performance paint with ABS flare assembly					
Assembly parts	adjustable stainless steel ratchet bracket providing positive setting					
Degree of protection	IP66, 4X					
Cable glands	UL units fitted with 2 x M20 to 1/2 inch NPT adaptors. All other units are supplied with ATEX approved stopping plug and dust cover					
Assembly / Installation						
Assembly	stainless steel mounting bracket provided. holes to suit M6. pitch 60 mm.					

Accessories and Spare Parts

Designation	Illustration	Description	Group	Order number	Art. no.	WebCode
Cable gland	14976E00	Compound Barrier Cable Glands Ex d and Ex e for all Types of Unarmoured Cables	IIB + H ₂ and IIC	8163/2-20- PXSS2K-M20	138888	8163J
	14742E00	Compound Barrier Cable Glands Ex d and Ex e for all Types of Armoured Cables	IIB + H ₂ and IIC	8163/2-20- PX2K-M20	138875	81631
	14977E00	Cable Glands Ex d and Ex e for Unarmoured Cables	IIB	8163/2-20- A2F-M20	138772	8163A
	14978E00	Triton CDS Cable Glands Ex d and Ex e for all Types of Armoured Cables	IIB	8163/2-20- T3CDS-M20	138902	8163K
Note	Approvals of ca	able entries have to be observed				

Dimensional Drawings (All Dimensions in mm / inches) - Subject to Alterations



We reserve the right to make alterations to the technical data, dimensions, weights, designs and products available without notice. The illustrations cannot be considered binding.