

Solid carbide quarter circle milling cutter

Concave

ORION[®]

Application:

Quarter circle milling cutter for machining complex forms, e.g. bore radii in materials up to 1300 N/mm².



Execution:

- Straight shank pursuant to DIN 1636 HA
- Tolerance R = +/- 0.01 mm

Art. no.	16711 915
Brand	ORION
Manufacturer Part Number	16711915
Cutting material	SC
Surface	TiAlN
Type	N
Number of cutting edges	4 PCS
Tool holding device	HA parallel shank
Radius	1.5 mm
Min. cutting edge diameter	7 mm
Max. cutting edge diameter	10 mm
Length	75 mm
Shank diameter	10 mm
fz steel 1000	0.017 mm
Gross Weight	0.085 kg
Product Group	150

EAN

4039247574094