VKP Series

HAY. www.vishay.com

Vishay Draloric

RoHS

COMPLIAN[®]

AC Line Rated Ceramic Disc Capacitors Class X1, 760 V_{AC} , Class Y1, 500 V_{AC}





QUICK REFERENCE DATA				
DESCRIPTION	VAI	LUE		
Ceramic Class	2	2		
Ceramic Dielectric	Y	5U		
Voltage (V _{AC})	760	500		
Min. Capacitance (pF)	47	70		
Max. Capacitance (pF)	47	00		
Mounting	Ra	dial		

MARKING

Marking indicates series, AC rating, capacitance, tolerance code, and approvals.

OPERATING TEMPERATURE RANGE

-40 °C to +125 °C

TEMPERATURE CHARACTERISTICS

Class 2 Y5U

SECTIONAL SPECIFICATIONS

Climatic category (according to EN 60058-1) Class 2 40/125/21

APPROVALS

IEC 60384-14.4 UL 60384-14.1 CSA E60384-1:03 2nd edition, CSA E60384-14:09 2nd edition

FEATURES

- Complying with IEC 60384-14 4th edition
- High reliability
- Wide range of different leadstyles
- Small dimensions
- Singlelayer AC disc safety capacitors
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

- X1, Y1 according to IEC 60384-14.4
- Across-the-line
- Line-by-pass
- Antenna coupling

DESIGN

The capacitors consist of ceramic disc both sides of which are silver plated. Connection leads are made of tinned copper having diameters of 0.6 mm or 0.8 mm.

The capacitors may be supplied with straight or kinked leads having a lead spacing of 10.0 mm or 12.5 mm.

Coating is made of blue colored flame retardant epoxy resin in accordance with UL 94 V-0.

CAPACITANCE RANGE

470 pF to 4.7 nF

TOLERANCE ON CAPACITANCE

± 10 %, ± 20 %

RATED VOLTAGE

- X1: 760 V_{AC}, 50 Hz (IEC 60384-14.4) 760 V_{AC}, 50 Hz / 60 Hz (US/UL/CSA 60384-14)
- Y1: 500 V_{AC}, 50 Hz (IEC 60384-14.4) 500 V_{AC}, 50 Hz / 60 Hz (US/UL/CSA 60384-14)

TEST VOLTAGE

- 4000 V_{AC}, 50 Hz, 2 s Component test (100 %)
- 4000 V_{AC}, 50 Hz, 60 s Random sampling test (destructive)
- 4000 V_{AC}, 50 Hz, 60 s Voltage proof of coating (destructive)

INSULATION RESISTANCE AT 500 V_{DC}

≥ 10 000 MΩ (60 s)

DISSIPATION FACTOR

Class 2: max. 2.5 % (1 kHz)

Revision: 29-Mar-18

1 For technical questions, contact: <u>slcap@vishay.com</u> Document Number: 22205


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



VKP Series

Vishay Draloric

DIMENSIONS in millimeters




TECHNICAL DATA							
	CAPACITANCE	BODY	BODY				PART NUMBER
C (pF) TOLERANCE DI		DIAMETER D _{MAX.} (mm)	THICKNESS S _{MAX.} (mm)	SPACING ⁽¹⁾ F (mm) ± 1 mm	DIAMETER ⁽¹⁾ d (mm) ± 0.05 mm	V (mm) ± 0.5 mm	MISSING DIGITS SEE ORDERING CODE BELOW
Y5U (2E3)	Y5U (2E3)						
470		8.0		12.5	0.6	2.1	VKP471#CQ###KR
680		8.0			0.6		VKP681#CQ###KR
1000		9.0			0.8		VKP102#CQ###KR
1500		10.0					VKP152#CQ###KR
2200	± 10, ± 20	12.0	5.0				VKP222#CQ###KR
2700		13.0					VKP272#CQ###KR
3300		15.0					VKP332#CQ###KR
3900		15.0					VKP392#CQ###KR
4700		17.0					VKP472#CQ###KR

Notes

⁽¹⁾ Standard lead configuration, other lead spacing and diameter available on request

⁽²⁾ When capacitance values less than 470 pF are required, the usage of WKP series is recommended

ORDERING CODE							
#	7 th digit	Capacitance tolerance		\pm 10 % = K, \pm 20 % = M			
###	10 th to 12 th digit	Lead configuration		see "General Information"			
Example	VKP	222	м	CQ	ED0	К	R
	Series	Capacitance value	Tolerance code	Voltage code	Lead configuration	Internal code	RoHS compliant



Revision: 29-Mar-18

2 For technical questions, contact: <u>slcap@vishay.com</u> Document Number: 22205


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000




Vishay Draloric

APPROVALS				
IEC 60384-14.4 - Safety tests This approval together with CB test certifi	cate substitutes all natio	nal approvals.		
CB Test Certificate Y1 Capacitor: CB-test certificate: X1 Capacitor: CB-test certificate: Minimum thickness of insulation: 0.4 mm	US-26551-UL US-26551-UL	470 pF to 4.7 nF 470 pF to 4.7 nF	500 V _{AC} 760 V _{AC}	(UL)
VDE Y1 Capacitor: VDE marks approval: X1 Capacitor: VDE marks approval:	136494 136494	470 pF to 4.7 nF 470 pF to 4.7 nF	500 V _{AC} 760 V _{AC}	
DIN EN 60384-14 VDE 0565-1-1:2006-04 Minimum thickness of insulation: 0.4 mm	- Safety tests			
Underwriters Laboratories Inc. / Canad	ian Standards Associat	ion		
Y1 Capacitor: UL-test certificate: X1 Capacitor: UL-test certificate:	E183844 E183844	470 pF to 4.7 nF 470 pF to 4.7 nF	500 V _{AC} 760 V _{AC}	œ — a ©
UL 60384-14.1, CSA E60384-1:03 2 nd edi Across-the-line, antenna-coupling and lin- Minimum thickness of insulation: 0.4 mm		2 nd edition		c 7 Us

LEAKAGE CURRENT VS. VOLTAGE (typical)



IMPEDANCE VS. FREQUENCY (typical)



RELATED DOCUMENTS				
General Information	www.vishay.com/doc?22001			
CB-Test Certificate	www.vishay.com/doc?22211			
VDE Marks Approval	www.vishay.com/doc?22212			
UL-Test Certificate	www.vishay.com/doc?22213			



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.