

Miniature cutting insert, type AF HW56 15

for axial recessing

ATORN[®]



Application

For axial recessing in the material groups of steel and (stainless steel) with low to high cutting speeds and medium cutting conditions.

Version

- solid carbide cutting insert with inner cooling

Advantage

- very hard cemented carbide type ensures low wear
- sturdy geometry for axial cutter insert
- extremely sharp cutting edges ensure cutting with process reliability

Art. no.	17131 224
Shaft diameter	6 mm
ISO name	AF
Length	58 mm
Clearance length	30 mm
Recessing width	3 mm
Plunge depth	6 mm
Programming size	2.95 mm
Min. bore diameter	8 mm
Machining direction	Right
Carbide type	HW56 15
Material to be processed	Stainless steel, Non-ferrous metal

EAN-Code

4050293379235