

ABI working island basic

With perforated metal plate wall for use on both sides



Application:

For accommodating tools, auxiliary material and utensils in the smallest possible area.

Execution:

- Frame rack made of 3 mm thick steel sheet, only 140 mm deep
- Perforated metal sheet wall with 10 x 10 mm square holes, 38 mm axis distance from hole centre to hole centre
- For add-on and equipment modules for individual equipping of the working islands see from no. 50238 886

Advantage:

- With the help of the versatile add-on and set-up modules, the workstations can be equipped individually on the basis of their operational requirements
- With the help of suitable holders and adapters, you mount all modules quickly and easily on the workstations and thus create an efficient, space-saving functional unit for optimisation of your production processes

Delivery:

Includes: Mounting feet set for anchoring to floor, double-sided perforated metal plate (rear can also be used)



Art. no.	50238 850
Brand	APFEL
Manufacturer Part Number	2332534
Model	1125 Basic
Width	1040 mm
Depth	140 mm
Height	2500 mm
Perforated plate width	910 mm
Perforated plate height	900 mm
Punched-hole	10 x 10 mm
Distance between centre of hole and centre of hole	38 mm
Equipped	No
Material	Sheet steel
Material thickness	3 mm
Colour of frame	Gentian blue RAL 50 10
Surface	Powder-coated
Gross Weight	0.001 kg
Product Group	586