

Indexable inserts, fine-boring rod, single tooth cutter, adjustable

for universal use up to 1300 N/mm² with CC..06 and CC..09..

ATORN[®]

Application

boring and drill out with CC.. indexable inserts in the diameter range from 10.00–50.00 mm in the material groups steel, stainless steel, non-ferrous metals, cast materials and special alloys.

Version

- Support material made from high-grade steel with adjusting range and clamping surface in line with DIN 1835B

Advantage

- low cost boring and reaming tool with large adjustment range
- standard CC.. indexable inserts can be used, thereby optimising procurement and minimising tool costs
- nickel-plated tool for high corrosion-resistance



Art. no.	11233 125
Number of cutting edges	1 PCS
Tool holding device	HB parallel shank
Min./max. cutting edge diameter	30-35 mm
Cantilever length	90 mm
Shaft length	70 mm
Length	160 mm
Shaft diameter	25 mm
Suitable for indexable inserts	CC..09

EAN-Code

4050293345650