

**Surface Mount Type**

Series: **ZC** Type: **V**

High temperature Lead-Free reflow



**Features**

- Endurance: 4000 h at 125 °C  
(The longest endurance in the industry by each case size)
- Low ESR and High ripple current (85% over, Lower ESR than Current V-TP)
- High-withstand voltage (25 V to 63 V), Low LC(0.01 CV or 3 μA)
- Equivalent to conductive polymer type Aluminum Electrolytic Capacitor  
(There are little characteristics change by temperature and frequency)
- RoHS directive compliant

**Specifications**

Category Temp. Range	-55 °C to +125 °C				
Rated W.V.Range	25 V.DC to 63 V.DC				
Nominal Cap.Range	10 μF to 330 μF				
Capacitance Tolerance	±20 % (120 Hz/+20 °C)				
DC Leakage Current	I ≤ 0.01 CV or 3 (μA) After 2 minutes (whichever is greater)				
tan δ	Please see the attached Standard Products list				
Endurance	The capacitor shall be subjected to application of the D.C. voltage with full rated ripple current at +125 °C for 4000 hours. After stabilizing at room temperature(+15 to 35 °C), the capacitor shall not exceed the specified limits. (The sum of DC voltage and ripple peak voltage shall not exceed the rated voltage.)				
	Capacitance change	±30 % of initial measured value			
	tan δ	≤ 200 % of initial specified value			
	E. S. R.	≤ 200 % of initial specified value			
	DC leakage current	≤ initial specified value			
ESR after Endurance (Ω/100 kHz) (-40 °C)	Size Code				
	C	D	D8	F	G
	2.0	1.4	0.8	0.4	0.3
Shelf Life	After storage for 1000 hours at +125 °C±2 °C with no voltage applied and then being stabilized at +20 °C, capacitors shall meet the limits specified in Endurance. (With voltage treatment)				
Resistance to Soldering Heat	After reflow soldering and then being stabilized at +20 °C, capacitors shall meet the following limits.				
	Capacitance change	±10 % of initial measured value			
	tan δ	≤ initial specified value			
	DC leakage current	≤ initial specified value			

**Frequency correction factor for ripple current**

	Frequency (Hz)			
	120	1 k	10 k	100 k to
Correction factor	0.10	0.30	0.60	1.00

**Marking**

Example: 25 V 33 μF Marking color : BLACK

Negative polarity marking (-)  
Capacitance (μF)  
Series identification  
Rated Voltage Mark  
Lot number

E	25 V
V	35 V
H	50 V
J	63 V

**Dimensions in mm (not to scale)**

( ) Reference size (mm)

Size code	D	L	A, B	H	I	W	P	K
C	5.0	5.8±0.3	5.3	6.5 max.	2.2	0.65±0.1	1.5	0.35 <sup>+0.15</sup> <sub>-0.20</sub>
D	6.3	5.8±0.3	6.6	7.8 max.	2.6	0.65±0.1	1.8	0.35 <sup>+0.15</sup> <sub>-0.20</sub>
D8	6.3	7.7±0.3	6.6	7.8 max.	2.6	0.65±0.1	1.8	0.35 <sup>+0.15</sup> <sub>-0.20</sub>
F	8.0	10.2±0.3	8.3	10.0 max.	3.4	0.90±0.2	3.1	0.70±0.2
G	10.0	10.2±0.3	10.3	12.0 max.	3.5	0.90±0.2	4.6	0.70±0.2

**NEW**

## ■ Standard Products

Endurance : 125 °C 4000 h

W.V. (V)	Cap. (±20 %) ( $\mu$ F)	Case size			Specification			Part No. (RoHS:compliant)	Reflow	Min. Packaging Q'ty
		Dia. (mm)	Length (mm)	Size Code	Ripple Current (100 kHz) (+125 °C) (mA r.m.s.)	E.S.R. (100 kHz) (+20 °C) (m $\Omega$ )	$\tan \delta$ (120 Hz) (+20 °C)			Taping  (pcs)
25	33	5	5.8	C	550	80	0.14	EEHZC1E330R	(5)	1000
	56	6.3	5.8	D	900	50	0.14	EEHZC1E560P	(5)	1000
	100	6.3	7.7	D8	1400	30	0.14	EEHZC1E101XP	(5)	900
	220	8	10.2	F	1600	27	0.14	EEHZC1E221P	(6)	500
	330	10	10.2	G	2000	20	0.14	EEHZC1E331P	(6)	500
35	22	5	5.8	C	550	100	0.12	EEHZC1V220R	(5)	1000
	47	6.3	5.8	D	900	60	0.12	EEHZC1V470P	(5)	1000
	68	6.3	7.7	D8	1400	35	0.12	EEHZC1V680XP	(5)	900
	150	8	10.2	F	1600	27	0.12	EEHZC1V151P	(6)	500
	270	10	10.2	G	2000	20	0.12	EEHZC1V271P	(6)	500
50	10	5	5.8	C	500	120	0.10	EEHZC1H100R	(5)	1000
	22	6.3	5.8	D	750	80	0.10	EEHZC1H220P	(5)	1000
	33	6.3	7.7	D8	1100	40	0.10	EEHZC1H330XP	(5)	900
	68	8	10.2	F	1250	30	0.10	EEHZC1H680P	(6)	500
	100	10	10.2	G	1600	28	0.10	EEHZC1H101P	(6)	500
63	10	6.3	5.8	D	700	120	0.08	EEHZC1J100P	(5)	1000
	22	6.3	7.7	D8	900	80	0.08	EEHZC1J220XP	(5)	900
	33	8	10.2	F	1100	40	0.08	EEHZC1J330P	(6)	500
	56	10	10.2	G	1400	30	0.08	EEHZC1J560P	(6)	500

The taping dimensions are explained on EE188 of our Catalog. Please use it as a reference guide.  
 Reflow Profile(Fig-5, Fig-6) listed on EE186 of our Catalog.