

MULTIPAL large-compartment rack

zinc-plated, with steel shelves



Execution:

- Large-compartment rack with steel shelves for storing individually packaged items of light to medium weight, not suitable for storing pallets
- Add-on rack, for expanding the basic rack
- 4 height-adjustable hook-clasps in 50 mm grid
- closed box-type profiles ensure high stability
- Rack type 85/20: Disassembled version, comprising cold-formed profiles, bolted to the bracing of the structure
- Basic rack planning dimensions: Total width = strut length + 170 mm, total depth = frame depth, planning dimension add-on shelf: Total width = strut length + 85 mm, total depth = frame depth
- Safety instructions: The loads indicated per shelf and per bay apply to uniformly distributed loads with at least 4 shelf bays and 2 strut pairs. Note: Steel panel shelves are not suitable for storing pallets.
- Colour: Galvanised rack, in RAL 5010 gentian blue upon request, struts in RAL 2001 red-orange

Delivery:

including floor anchor



Art. no.	50171 121
Brand	META
Manufacturer Part Number	20077552
Height	2700 mm
Depth	800 mm
Nominal length	2700 mm
Type of shelving	Add-on shelving
Design	With steel panel
Type of assembly	Screw mounting
Surface	Zinc plated
ESD-capable	No
Design of the frame	Disassembled
Grid dimension	50 mm
Number of shelves	4 PCS
Load-carrying capacity per shelf	2400 kg
Load-carrying capacity per field	10100 kg
Number of frame	1 PCS
Quality label	RAL-RG 614/2
Made in	Germany
Product certification	Institute for Materials Research and Testing (MPA) North Rine Westphalia (NRW) (Dortmund)
Approval mark	GS - MPA NRW
Approval mark - Product certification	GS - MPA NRW - Institute for Materials Research and Testing (MPA) North Rine Westphalia (NRW) (Dortmund)
Gross Weight	240.637 kg
Product Group	508

EAN

4026212132700