

[IMAGE]

Product Information

Product Category	REFRIGERATION
Unit Barcode	5016368003091
Outer Carton Barcode	
Commodity Code	8418402091
Country of Origin	CHINA
Primary Colour	WHITE
Finish	PAINTED STEEL
Primary Material	STAINLESS STEEL
Warranty	2
Self Assembly	NO
Perishable Item	NO
Hazardous Item	NO

General Product Specification

Voltage	230
Frequency	50
Wattage	100
Rated Current	0.7
Fuse Rating	13
Plug Type	BS 1363
Cable Diameter	0.75
Cable Length	1
Class	CLASS I
Conformity Markings	CE+UKCA

Packaging & Shipping Information

Product Dimensions H x W x D (mm)	850	480	450
Packaged Dimensions H x W x D (mm)	952	533	510
Outer Carton Dimensions H x W x D (mm)			
Outer Carton Qty.			
Unit Weight (Kg)			23
Unit Packaged Weight (Kg)			25
Carton Weight (Kg)			
EPS (Kg)	1.045	PPT Exempt Plastic (Kg)	
Other Plastic (Kg)	0.23	Card / Paper (Kg)	1
Aluminium (Kg)		Steel (Kg)	0.012

Category Specific Technical Information

Type	OTHER REFRIGERATING APPLIANCE	Number of Freezer Compartments	3
Design Type	FREESTANDING	Number of Fridge Shelves	
Gross Total Volume	60	Door Hinge Position	
Net Total Volume	60	Reversible Door	YES
Net Refrigeration Volume		Door Handle Colour	WHITE
Net Freezing Volume	60	Door Handle Material	ABS
Energy Efficiency Index	99.4	Door Material	METAL
Energy Rating	E	Door Opening Angle	135
Airborne Acoustical Noise Emission Class		Housing Colour	WHITE
Annual Energy Consumption	156	Lamp Rated Power	
Climate Class	ST	LED Lighting	NO
Minimum Ambient Operating Temperature	16	Power Failure Safe Storage	
Maximum Ambient Operating Temperature	38	Temperature Rise Time	7.5
Winter Setting	NO	Thermostat Temperature Range	-22 TO -18
Freezer Star Rating	4	Thermostat Type	MECHANICAL
Fast Freeze Facility	NO	Refrigerant Type	R600A
Freezing Capacity	2.8	Refrigerant Amount	36
Defrosting Type	MANUAL	RF: Back Panel Material	FULL METAL
Freezer Technology	STATIC		