

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1053001200](#)
Status: **Active**
Overview: [Nano-Fit Power Connectors](#)
Description: Nano-Fit Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 24-26 AWG

Documents:

Drawing (PDF)	Test Summary 1053000000-TS-000 (PDF)
Product Specification PS-105300-100-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-105300-100-000 (PDF)	Product Literature (PDF)

General

Product Family	Crimp Terminals
Series	105300
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	Nano-Fit Power Connectors
Product Literature Order No	987651-1223
Product Name	Nano-Fit
UPC	889056003254

Physical

Durability (mating cycles max)	50
Gender	Female
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin over Nickel
Net Weight	0.100/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30mm
Wire Size AWG	24, 26
Wire Size mm ²	0.13-0.20

Electrical

Current - Maximum per Contact	6.5A
Voltage - Maximum	250V AC (RMS)

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-105300-100-000
Product Specification	PS-105300-100-001
Sales Drawing	SD-105300-100-000
Test Summary	1053000000-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[105300 Series](#)

Use With

Nano-Fit Receptacle Housing [105307](#) ,
[105308](#)