


PU5460



Pressure transmitter

PU-600-SEG14-B-DVG/US /W



1 Sealing



Product characteristics

Output signal	analogue signal		
Measuring range	0...600 bar	0...8700 psi	0...60 MPa
Process connection	threaded connection G 1/4 external thread (DIN EN ISO 1179-2)		

Application

Application	for industrial applications		
Media	liquids and gases		
Medium temperature [°C]	-40...90		
Pressure rating	1500 bar	21755 psi	150 MPa
Note on pressure rating		static	
Min. bursting pressure	2500 bar	36255 psi	250 MPa
Vacuum resistance [mbar]		-1000	
Type of pressure	relative pressure		

Electrical data

Operating voltage [V]	16...36 DC		
Current consumption [mA]	< 12		
Min. insulation resistance [MΩ]	100; (500 V DC)		
Protection class	III		
Reverse polarity protection	yes		

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1
------------------------------	-------------------------------

PU5460



Pressure transmitter

PU-600-SEG14-B-DVG/US /W

Outputs		
Total number of outputs		1
Output signal		analogue signal
Number of analogue outputs		1
Analogue voltage output [V]		0...10
Min. load resistance [Ω]		2000
Short-circuit proof		yes
Overload protection		yes
Measuring/setting range		
Measuring range	0...600 bar	0...8700 psi
		0...60 MPa
Accuracy / deviations		
Repeatability [% of the span]		< ± 0,05; (with temperature fluctuations < 10 K)
Characteristics deviation [% of the span]		< ± 0,5; (incl. drift when overtightened, zero point and span error, non-linearity, hysteresis)
Linearity deviation [% of the span]		< ± 0,1 (BFSL) / < ± 0,2 (LS)
Hysteresis deviation [% of the span]		< ± 0,2
Long-term stability [% of the span]		< ± 0,1; (per 6 months)
Temperature coefficient zero point and span [% of the span / 10 K]		< ± 0,1 (-25...90 °C) / < ± 0,2 (-40...-25 °C)
Response times		
Step response time analogue output [ms]		1
Operating conditions		
Ambient temperature [°C]		-40...90
Storage temperature [°C]		-40...100
Protection		IP 67; IP 69K
Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF [years]		762
UL approval	UL Approval no.	J030
Pressure Equipment Directive	Modul A; can be used for group 2 fluids; group 1 fluids on request	

PU5460



Pressure transmitter

PU-600-SEG14-B-DVG/US/ /W

Mechanical data

Weight	[g]	60
Materials		1.4542 (17-4 PH / 630); stainless steel (1.4404 / 316L); PEI
Materials (wetted parts)		1.4542 (17-4 PH / 630)
Min. pressure cycles		60 million; (at 1.2 times nominal pressure)
Tightening torque	[Nm]	30...50; (recommended tightening torque; depends on lubrication, seal and pressure rating)
Process connection		threaded connection G 1/4 external thread (DIN EN ISO 1179-2)
Process connection sealing		FKM (to DIN 3869)
Restrictor element integrated		no (can be retrofitted)

Remarks


Remarks	BFSL = Best Fit Straight Line LS = limit value setting
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12



Connection



OUT	analogue output colours to DIN EN 60947-5-2 Core colours :
BN =	brown
BU =	blue
WH =	white