



Hyspin ZZ Range

Anti-wear Hydraulic Oil

Description

The Castrol Hyspin™ ZZ hydraulic oil range of lubricants are formulated without zinc containing additives, based on a carefully selected additive system, designed to meet and exceed the most exacting performance standards.

Application

The Hyspin ZZ range are formulated for applications requiring anti-wear and superior oxidation performance and are particularly suitable for hydraulic systems using vane and piston pumps where elevated operating temperatures are encountered. They are formulated for use in severely stressed systems in which high levels of anti-wear performance and/or ultra fine filtration are required. They have been proven to be resistant to the effects of 'dieseling' in highly stressed systems such as plastic injection moulding and fatigue testing equipment where the application leads to rapid breakdown of more conventional products.

The range is fully compatible with elastomer materials commonly used for static and dynamic seals, such as nitrile, silicone and fluorinated (e.g. Viton) polymers.

Hyspin ZZ is classified as follows:

- DIN 51502 classification - HLP
- ISO 6743/4 - Hydraulic Oils Type HM

Hyspin ZZ (for appropriate viscosity grade) is approved by:

- Parker Hannifin (Denison) HF0, HF1 & HF2
- Eaton E-FDGN-TB002-E

Hyspin ZZ grades meet the requirements (for appropriate viscosity grade) of:

- DIN 51524 Part 2
- Fives Cincinnati P68, P69 & P70
- ASTM D6158 HM
- ISO 11158 HM
- US Steel 126
- GB 11118.1 L-HM (General and High Pressure)

Advantages

- Good thermal and oxidative stability provides reliable performance and extended oil life in severe applications. Minimal deposit formation gives a cleaner system and reduced frequency of filter changes.
- Excellent anti-wear performance provides extended wear protection for hydraulic pumps. Reduced downtime due to unscheduled maintenance and savings from replacement part costs.
- Excellent filterability characteristic (including in the presence of water) enables cost savings to be made from increased filter life and reduced maintenance.
- Excellent water separation and hydrolytic stability means reduced down time through prolonged lubricant life and increased equipment reliability.

Typical Characteristics

Name	Method	Units	ZZ 100
ISO Viscosity Grade	-	-	100
Density @ 15°C / 59°F	ISO 12185 / ASTM D4052	kg/m ³	880
Kinematic Viscosity @ 40°C / 104°F	ISO 3104 / ASTM D445	mm ² /s	100
Kinematic Viscosity @ 100°C / 212°F	ISO 3104 / ASTM D445	mm ² /s	11.1
Viscosity Index	ISO 2909 / ASTM D2270	-	>95
Pour Point	ISO 3016 / ASTM D97	°C/°F	-21/-6
Flash Point - open cup method	ISO 2592 / ASTM D92	°C/°F	225/437
Flash Point - closed cup method	ISO 2719 / ASTM D93	°C/°F	220/428
Foam Sequence I - tendency / stability	ISO 6247 / ASTM D892	ml/ml	20/0
Water Separation @ 54°C / 129°F (40/37/3)	ISO 6614 / ASTM D1401	min	-
Water Separation @ 82°C / 180°F (40/37/3)	ISO 6614 / ASTM D1401	min	15
Air Release @ 50°C / 122°F	ISO 9120 / ASTM D3427	min	12
FZG Gear Scuffing test - A/8.3/90	ISO 14635-1	Failure Load Stage	12
Rust test - distilled water (24 hrs)	ISO 7120 / ASTM D665A	-	Pass
Rust test - synthetic seawater (24 hrs)	ISO 7120 / ASTM D665B	-	Pass
Oxidation Stability - TOST	ISO 4263-1 / ASTM D943	hrs	-

Subject to usual manufacturing tolerances.

Hyspin ZZ Range

14 Jul 2021

Castrol, the Castrol logo and related marks are trademarks of Castrol Limited, used under licence.

This data sheet and the information it contains is believed to be accurate as of the date of printing. However, to the extent that it is permissible by law to exclude warranties and representations, no warranty or representation, express or implied, is made as to its accuracy or completeness. Data provided is based on standard tests under laboratory conditions and is given as a guide only. Users are advised to ensure that they refer to the latest version of this data sheet. It is the responsibility of the user to evaluate and use products safely, to assess suitability for the intended application and to comply with all applicable laws and regulations. Material Safety Data Sheets are available for all our products and should be consulted for appropriate information regarding storage, safe handling, and disposal of the product. Refer to the MSDS, available from our website for further information. No responsibility is taken by either Castrol Australia, BP plc or its subsidiaries for any damage or injury resulting from abnormal use of the material, from any failure to adhere to recommendations, or from hazards inherent in the nature of the material. All products, services and information supplied are provided under our standard conditions of sale. You should consult our local representative if you require any further information.

Castrol Australia Pty Limited - ABN 87 008 459 407 – 717 Bourke Street, Docklands Vic 3008

Technical Advice Line: 1300 557 998 Customer Service: 1300 722 088

<http://msdspdscastrol.com>

Page: 2/2