

NON-SPARKING HAMMERS



EGA Master Non-Sparking Tools are the best alternative for non-sparking application purposes in potentially explosive environments. All tools are forged after casting to achieve the best quality in the market, both in mechanical properties and attractive finishing.

1. This is an ideal solution for striking operations in potentially explosive environments.



2. Conical handle to avoid head coming out.

3. Safety pin for fixing the head.

4. Ultra-resistant fiberglass handle core.

5. Outer PP coating and TPR antislippery handle.

6. Hardness in striking face: 283-365 Brinell (Cu-Be) and 229-291 Brinell (Al-Bron).



EGA Master has renewed its range of wooden and fiberglass handles to satisfy the demand from the most professional user. The **handle-head fixation is reinforced** in both handle types, completely avoiding the disattachment of the head from the handle. Their manufacturing materials guarantee a durable use.

For these reasons, **EGA Master** handles are a quality guarantee for industrial uses

BALL PEIN HAMMER



| COD | | L mm | gr. |
|-------|---------|---------|-----|
| Cu-Be | Al-Bron | | |
| 70488 | 71743 | 280 | 200 |
| 70489 | 71744 | 310 | 500 |
| 70490 | 71745 | 340 | 700 |
| 70491 | 71746 | 350 | 900 |

ENGINEER'S CROSS PEIN HAMMER



| COD | | L mm | gr. |
|-------|---------|---------|-----|
| Cu-Be | Al-Bron | | |
| 70492 | 71747 | 310 | 500 |
| 70493 | 71748 | 350 | 900 |

GERMAN TYPE MACHINIST'S HAMMER



| COD | | L mm | gr. |
|-------|---------|---------|------|
| Cu-Be | Al-Bron | | |
| 70494 | 71749 | 300 | 100 |
| 70495 | 71750 | | 200 |
| 70496 | 71751 | | 300 |
| 70497 | 71752 | 310 | 500 |
| 70498 | 71753 | | 800 |
| 70499 | 71754 | | 1000 |
| 70500 | 71755 | 400 | 1500 |
| 70501 | 71756 | 450 | 2000 |

SLEDGE HAMMER



| COD | | L mm | Kg. |
|-------|---------|---------|-----|
| Cu-Be | Al-Bron | | |
| 70502 | 71757 | 370 | 1 |
| 70503 | 71758 | | 1,5 |
| 70504 | 71759 | | 2,0 |
| 70505 | 71760 | 850 | 2,5 |
| 70506 | 71761 | | 3,0 |
| 70507 | 71762 | | 4,5 |
| 70508 | 71763 | | 5,0 |
| 70509 | 71764 | | 6,8 |
| 70510 | 71765 | | 8,0 |
| 72213 | 72211 | 900 | 10 |
| 72975 | 72974 | | 12 |

GERMAN TYPE STONING HAMMER



| COD | | L mm | Kg. |
|-------|---------|---------|-----|
| Cu-Be | Al-Bron | | |
| 70511 | 71766 | 400 | 1 |
| 70512 | 71767 | | 1,5 |
| 70513 | 71768 | | 2 |
| 70514 | 71769 | 860 | 2,5 |
| 70515 | 71770 | | 3 |
| 72098 | 72099 | | 3,5 |

CUT-OFF HAMMER



| COD | | L mm | Kg. |
|-------|---------|---------|-----|
| Cu-Be | Al-Bron | | |
| 70516 | 71771 | 400 | 1,3 |
| 70517 | 71772 | | 2,1 |

CHIPPING HAMMER



| COD | | L mm | gr. |
|-------|---------|---------|-----|
| Cu-Be | Al-Bron | | |
| 70518 | 71773 | 280 | 200 |
| 70519 | 71774 | 355 | 400 |
| 70520 | 71775 | | 600 |
| 70521 | 71776 | 400 | 900 |

STONE WEDGE



| COD | | L mm | Kg. |
|-------|---------|---------|-----|
| Cu-Be | Al-Bron | | |
| 70522 | 71777 | 400 | 1 |

BRICKLAYER'S HAMMER



| COD | | L mm | gr. |
|-------|---------|---------|-----|
| Cu-Be | Al-Bron | | |
| 70523 | 71778 | 340 | 600 |
| 70524 | 71779 | | 800 |

CLAW HAMMER



| COD | | L mm | gr. |
|-------|---------|---------|-----|
| Cu-Be | Al-Bron | | |
| 70525 | 71780 | 275 | 500 |
| 70526 | 71781 | 338 | 700 |

NYLON HAMMER



| COD | | mm | L mm | gr. |
|-------|---------|----|---------|------|
| Cu-Be | Al-Bron | | | |
| 70527 | 71782 | 50 | 340 | 800 |
| 73473 | 73393 | 55 | 400 | 1000 |

TESTING HAMMER



| COD | | L mm | gf. |
|-------|---------|---------|-----|
| Cu-Be | Al-Bron | | |
| 75211 | 75212 | 390 | 125 |
| 75214 | 75213 | 420 | 250 |

SLEDGE HAMMER



| COD | | L mm | gf. |
|-----------|-----|---------|-------|
| Lat/Brass | | | |
| 72740 | | 280 | 300 |
| 72741 | | 310 | 500 |
| 72742 | | | 1000 |
| 72743 | 400 | | 1500 |
| 72744 | | | 2000 |
| 72745 | | | 3000 |
| 72746 | | | 4000 |
| 72747 | 900 | | 5000 |
| 72748 | | | 7000 |
| 72749 | | | 10000 |



| COD | | L mm | gf. |
|-------|-----|---------|-------|
| Cu | | | |
| 72750 | | 350 | 450 |
| 72751 | | 400 | 1000 |
| 72752 | | 800 | 2500 |
| 72753 | | | 3600 |
| 72754 | | | 4500 |
| 72755 | 900 | | 5400 |
| 72756 | | | 6400 |
| 72757 | | | 10000 |

DRUM TYPE STONING HAMMER



| COD | | L mm | gf. |
|-------|--|---------|------|
| Cu | | | |
| 72758 | | 280 | 300 |
| 72759 | | 310 | 570 |
| 72760 | | 340 | 810 |
| 72761 | | 350 | 1100 |
| 72762 | | 400 | 1600 |
| 72763 | | | 2300 |

GERMAN TYPE STONING HAMMER



| COD | | L mm | gf. |
|-----------|-------|---------|------|
| Lat/Brass | Cu | | |
| 72764 | 72773 | 350 | 500 |
| 72765 | 72774 | | 1000 |
| 72766 | 72775 | 400 | 1500 |
| 72767 | 72776 | | 1800 |
| 72768 | 72777 | | 2000 |
| 72769 | 72778 | | 2700 |
| 72770 | 72779 | 900 | 3600 |
| 72771 | 72780 | | 4000 |
| 72772 | 72781 | | 5000 |

BALL PEIN HAMMER



| COD | | L mm | gr. |
|-----------|-------|---------|------|
| Lat/Brass | Cu | | |
| 72782 | 72788 | 280 | 230 |
| 72783 | 72789 | | 340 |
| 72784 | 72790 | 310 | 450 |
| 72785 | 72791 | 340 | 680 |
| 72786 | 72792 | 350 | 910 |
| 72787 | 72793 | 400 | 1130 |

SCALING HAMMER



| COD | | L mm | gr. |
|-----------|----|---------|-----|
| Lat/Brass | Cu | | |
| 72794 | | 330 | 205 |
| 72795 | | 350 | 370 |

BRASS MALLET



| COD | | L mm | gr. |
|-----------|----|---------|------|
| Lat/Brass | Cu | | |
| 72796 | | 900 | 4500 |
| 72797 | | | 5400 |
| 72798 | | | 7650 |

COPPER MALLET



| COD | | L mm | gr. |
|-------|--|---------|------|
| Cu | | | |
| 72799 | | 350 | 1350 |

ANVIL BLOCK



| COD | | | Kg. |
|-------|---------|-------------|-----|
| Cu-Be | Al-Bron | AxBxC (mm) | |
| 73734 | 73735 | 92x92x63 | 3 |
| 73736 | 73737 | 111x111x75 | 5 |
| 73738 | 73739 | 160x160x114 | 16 |

Cu-Be Beryllium copper

Al-Bron Aluminium bronze

Lat/Brass Brass

Cu Copper