





Control Stations

Characteristics

General Characteristics


Products	Control Stations
Reference Standard	IEC 60947-5-1, EN 60947-5-1, IEC 337-1, UL 508, CSA C-22-2 n° 14
Approval	  & 
Protection Degree	IP 65 / IP 66 (as per IEC), NEMA 4 / 4X (special version)
Ambient Temperature	-40°C ~ + 70°C (Storage) -25°C ~ +70°C (Operation)
Vibration Resistance	15g (40 To 500 Hz) conforming to IEC 68-2-6
Shock Resistance	Push Buttons : 70g, Mushroom Head Push Buttons : 15g, Selector Switches : 200g conforming to IEC 68-2-27
Material and Colour	Thermoplastic - grey lid and black base for 1,2,3,4 way, yellow lid & black base for one way Aluminium Die Cast - grey lid and dark grey base
Cable Entry	Knock-outs provided




RC-2P



RC-1M



RC-4P





















RC-3M




RC-1PY

Stations for customer assembly

Empty Control Station Enclosures for customer assembly in plastic & metal

Description	No. of Holes	Colour	Reference
CONTROL STATION PLASTIC ENCLOSURE	1	LID 	RC-1P
		BASE 	
	2	LID 	RC-2P
		BASE 	
	3	LID 	RC-3P
		BASE 	
	4	LID 	RC-4P
		BASE 	
1	LID 	RC-1PY	
	BASE 		
CONTROL STATION METAL ENCLOSURE	1	LID 	RC-1M
		BASE 	
	2	LID 	RC-2M
		BASE 	
	3	LID 	RC-3M
		BASE 	
	4	LID 	RC-4M
		BASE 	



C&S Control Station Dimensions

Plastic					Metal			
Measure	1 Hole	2 Hole	3 Hole	4 Pole	1 Hole	2 Hole	3 Hole	4 Hole
H	51mm				51mm			
W	68mm				68mm			
L	74mm	104mm	134mm	164mm	74mm	105mm	134mm	164mm
W 1	54mm				54mm			
L 1	38mm	68mm	68mm	128mm	46mm	78mm	108mm	138mm