

## BLINDNIETE



FLACHRUNDKOPF (~ DIN EN ISO 15977)

## BLIND RIVETS

DOMED HEAD (~ DIN EN ISO 15977)

## RIVETS AVEUGLES

TÊTE PLATE (~ DIN EN ISO 15977)



Aluminium AIMG 3,5  
Aluminium AIMG 3,5  
Aluminium AIMG 3,5

Stahl verzinkt  
Steel zinc plated  
Acier zingué

### Ø 4,0 mm

D1 = 4,0 + 0,08 / - 0,15 mm  
D2 = 8,0 + 0 / - 1,0 mm  
k = 1,0 + / - 0,3 mm  
d = 2,1 mm  
P = ≥ 27,0 mm  
L = + 1,0 / - 0,2 mm  
 4,1 mm

	F-Max		CODE				
4,0 x 6,0 mm	10,9 mm	1,5 - 3,0 mm	70701 40600	1100 N	1400 N	1000	10000
4,0 x 7,0 mm	11,9 mm	2,0 - 4,0 mm	70701 40700			1000	10000
4,0 x 8,0 mm	12,9 mm	3,0 - 5,0 mm	70701 40800			1000	10000
4,0 x 10,0 mm	14,9 mm	5,0 - 6,5 mm	70701 40100			1000	10000
4,0 x 12,0 mm	16,9 mm	6,5 - 8,5 mm	70701 40120			1000	10000
4,0 x 14,0 mm	18,9 mm	8,5 - 10,5 mm	70701 40140			500	5000
4,0 x 16,0 mm	20,9 mm	10,5 - 12,5 mm	70701 40160			500	5000
4,0 x 18,0 mm	22,9 mm	12,5 - 14,5 mm	70701 40180			500	5000
4,0 x 20,0 mm	24,9 mm	14,5 - 16,5 mm	70701 40200			500	5000
4,0 x 23,0 mm	27,9 mm	16,5 - 19,0 mm	70701 40230			500	5000
4,0 x 25,0 mm	29,9 mm	19,0 - 21,5 mm	70701 40250	850 N	1000 N	500	5000
4,0 x 30,0 mm	34,9 mm	21,5 - 26,0 mm	70701 40300			500	5000
4,0 x 35,0 mm	39,9 mm	26,0 - 30,0 mm	70701 40350			500	5000

### Ø 4,8 mm

D1 = 4,8 + 0,08 / - 0,15 mm  
D2 = 9,5 + 0 / - 1,0 mm  
k = 1,1 + / - 0,3 mm  
d = 2,7 mm  
P = ≥ 27,0 mm  
L = + 1,0 / - 0,2 mm  
 4,9 mm

	F-Max		CODE				
4,8 x 6,0 mm	11,4 mm	1,0 - 3,0 mm	70701 48600	1500 N	1900 N	500	5000
4,8 x 8,0 mm	13,4 mm	3,0 - 4,5 mm	70701 48800			500	5000
4,8 x 10,0 mm	15,4 mm	4,5 - 6,0 mm	70701 48100			500	5000
4,8 x 12,0 mm	17,4 mm	6,0 - 8,0 mm	70701 48120			500	5000
4,8 x 14,0 mm	19,4 mm	8,0 - 10,0 mm	70701 48140			500	5000
4,8 x 16,0 mm	21,4 mm	10,0 - 12,0 mm	70701 48160			500	5000
4,8 x 18,0 mm	23,4 mm	12,0 - 14,0 mm	70701 48180			500	5000
4,8 x 20,0 mm	25,4 mm	14,0 - 16,0 mm	70701 48200			500	5000
4,8 x 22,0 mm	27,4 mm	16,0 - 18,0 mm	70701 48220			500	5000
4,8 x 25,0 mm	30,4 mm	18,0 - 21,0 mm	70701 48250			500	5000
4,8 x 28,0 mm	33,4 mm	21,0 - 23,5 mm	70701 48280	250	2500		
4,8 x 30,0 mm	35,4 mm	23,0 - 25,0 mm	70701 48300	250	2500		
4,8 x 35,0 mm	40,4 mm	25,0 - 30,0 mm	70701 48350	1200 N	1700 N	250	2500
4,8 x 40,0 mm	45,4 mm	30,0 - 35,0 mm	70701 48400			250	2500
4,8 x 45,0 mm	50,4 mm	35,0 - 40,0 mm	70701 48450			100	1000
4,8 x 50,0 mm	55,4 mm	40,0 - 45,0 mm	70701 48500			100	1000
4,8 x 55,0 mm	60,4 mm	45,0 - 50,0 mm	70701 48550			100	1000
4,8 x 60,0 mm	65,4 mm	50,0 - 55,0 mm	70701 48610			100	1000
4,8 x 65,0 mm	70,4 mm	55,0 - 60,0 mm	70701 48650			100	1000