

Collet chuck extension

With internal cooling and straight shank, type ER Mini

diebold

Application:

For clamping tools with straight shank.

Execution:

- With straight shank, type ER Mini.
- Particularly slim version for use in milling chucks as tool extension for deep machining operations where space is restricted.
- Straight shank made of solid material.
- Hollow bored for internal cooling.

Delivery:

1x collet chuck extension.



Art. no.	23304 005
Brand	DIEBOLD
Manufacturer Part Number	74.020.005
Collet type	ER 16
Shank diameter	10 mm
Min./max. clamping range	0.5-10 mm
Outer diameter	22 mm
Shaft length	60 mm
Length of head	38 mm
Gross Weight	0.045 kg
Product Group	2AB