

precision sine vices, type PS-SV

Actuated via trapezoidal spindle



Application:

For grinding and inspection tasks.

Execution:

- Made of alloyed tool steel.
- Hardened and precision-ground.
- Squareness tolerance 0.005 mm/100 mm and parallelism tolerance 0.002 mm/100 mm.
- Precise angular adjustment achieved using gauge blocks (see no. 32050 onwards).
- Angular deviation at $45^\circ \pm 15$ arc seconds.
- Hardened and polished bearing and mounting bolts with a tolerance of 0.001 mm.
- The clamp can be positively locked at any angle.
- Drawing „W“= 2 x M5x15.

Delivery:

1x precision sine vice, type PS-SV



Art. no.	28620 010
Brand	RÖHM
Manufacturer Part Number	370778
Model	PS-SV 70
Prism countersunk horizontally	Yes
Jaws width	70 mm
Jaws height	30 mm
Height 2	63 mm
Clamping width	80 mm
Height	93 mm
Body length	160 mm
Length 2	33 mm
Length 3	45 mm
Section, length	100 mm
Min./max. angle scale	0-46 Degree
Gross Weight	5.822 kg
Product Group	202

EAN

4019208094885