

# RSF50 SERIES

## COMPACT INTERNAL FITTING VERTICAL



RSF50 series are compact vertically mounted devices with a single switch point. Mounting is either from the top or bottom of a tank from the inside, so requires access to the inside of the tank.

Typical applications include vending machines, printing systems and chemical dosing equipment.

These can be manufactured in a variety of plastics, with a choice of gasket materials, to suit most commonly used liquids.

The switch action may be reversed by removing the float, inverting it, then refitting to the stem.

Available with M12 x 1.75 or 1/8"NPT mounting threads.

#### **Features**

- Compact design
- Available in Nylon, Polypropylene, PPS & PVDF
- 3VA, 25VA & 100VA versions
- Many variants are UL recognised components File No. E171218
- WRAS and NSF approved versions
- 1/8" NPT and M12 thread options



### **Technical**

		RSF53	RSF54	RSF58	RSF56	RSF57
Material		Nylon	Polypropylene	Polypropylene	Polyphenylene	Polyvinylidene
			WRAS approved	UL approved	Sulphide (PPS)	Fluoride (PVDF)
Colour		Black	Opaque	White	Grey	Green
Temp. Range °C		-20/+75	-20/+100	-20/+100	-10/+120*	-10/+105
	°F	-4/+167	-4/+212	-4/+212	+14/+248*	+14/+221
Min. Fluid SG		0.8	0.65	0.65	0.85	0.85
Must Close Level (SG=1)		11.5mm	15mm	15mm	9.5mm	9.5mm
Must Open Level (SG=1)		22.5mm	26mm	26mm	20.5mm	20.5mm

<sup>\*</sup> Maximum temperature requires ETFE cable to be specified, otherwise +105°C.



## Electrical

		3W (V Code)	25W (Y code)	100W (H code)
Contact Form		C/O	N/O (N/C)	N/O (N/C)
Switching Power Max	VA	3	25	100
Switching Voltage AC Max	V	-	240	300
Switching Voltage DC Max	V	100	120	300
Switching Current Max	Α	0.25	0.6	1

All ratings are for resistive load only.




	Material	Temp Range	Max Power	<b>Mounting Thread</b>	Leadouts	Gasket	Approvals
RSF53H100RC	Nylon	-20°C to +75°C	100VA	M12	100cm PVC 16/0.2	Nitrile	WRAS
RSF53H100R1/8	Nylon	-20°C to +75°C	100VA	1/8" NPT	100cm PVC 16/0.2	N/A	WRAS
RSF53V100MC	Nylon	-20 C to +75°C	3VA	M12	100 cm Cable 3-Core 7/0.2	Nitrile	WRAS
RSF53Y100JC	Nylon	-20 C to +75°C	25VA	M12	100 cm Cable 2-Core 7/0.2	Nitrile	WRAS
RSF53Y100RC	Nylon	-20°C to +75°C	25VA	M12	100cm PVC 16/0.2	Nitrile	WRAS
RSF53Y100R1/8	Nylon	-20°C to +75°C	25VA	1/8" NPT	100cm PVC 16/0.2	N/A	WRAS
RSF54H100RC	PP	-20°C to +100°C	100VA	M12	100cm PVC 16/0.2	Nitrile	WRAS & NSF
RSF54H100R1/8	PP	-20°C to +100°C	100VA	1/8" NPT	100cm PVC 16/0.2	N/A	WRAS & NSF
RSF54V100MC	PP	-20 C to +100°C	3VA	M12	100 cm Cable 3-Core 7/0.2	Nitrile	WRAS & NSF
RSF54Y100JC	PP	-20 C to +100°C	25VA	M12	100 cm Cable 2-Core 7/0.2	Nitrile	WRAS & NSF
RSF54Y100RC	PP	-20°C to +100°C	25VA	M12	100cm PVC 16/0.2	Nitrile	WRAS & NSF
RSF54Y100R1/8	PP	-20°C to +100°C	25VA	1/8" NPT	100cm PVC 16/0.2	N/A	WRAS & NSF
RSF56H050TB	PPS	-10°C to +120°C	100VA	M12	50cm ETFE 19/0.2	Viton	UL & NSF
RSF56H100RC	PPS	-10°C to +105°C	100VA	M12	100cm PVC 16/0.2	Nitrile	WRAS, UL & NSF
RSF56H100R1/8	PPS	-10°C to +105°C	100VA	1/8" NPT	100cm PVC 16/0.2	N/A	WRAS, UL & NSF
RSF56Y050TB	PPS	-10°C to +120°C	25VA	M12	50cm ETFE 19/0.2	Viton	UL & NSF
RSF56Y050T1/8	PPS	-10°C to +120°C	25VA	1/8" NPT	50cm ETFE 19/0.2	N/A	WRAS, UL & NSF
RSF56Y100TB	PPS	-10°C to +120°C	25VA	M12	50cm ETFE 19/0.2	Viton	UL & NSF
RSF56Y100RB	PPS	-10 C to +105°C	25VA	M12	100 cm PVC 16/0.2	Viton	UL & NSF
RSF56Y100RC	PPS	-10°C to +105°C	25VA	M12	100cm PVC 16/0.2	Nitrile	WRAS, UL & NSF
RSF56Y100R1/8	PPS	-10°C to +105°C	25VA	1/8" NPT	100cm PVC 16/0.2	N/A	WRAS, UL & NSF
RSF57H100GC	PVDF	-10°C to +105°C	100VA	M12	100cm PTFE7/0.2	Nitrile	UL & NSF
RSF57H100G1/8	PVDF	-10°C to +105°C	100VA	1/8" NPT	100cm PTFE7/0.2	N/A	UL & NSF
RSF57Y100GC	PVDF	-10°C to +105°C	25VA	M12	100cm PTFE7/0.2	Nitrile	UL & NSF
RSF57Y100G1/8	PVDF	-10°C to +105°C	25VA	1/8" NPT	100cm PTFE7/0.2	N/A	UL & NSF
RSF57H100GB	PVDF	-10°C to +105°C	100VA	M12	100cm PTFE7/0.2	Viton	UL & NSF
RSF57Y100GB	PVDF	-10°C to +105°C	25VA	M12	100cm PTFE7/0.2	Viton	UL & NSF
RSF58H100JC	PP (UL)	-20 C to +100°C	100VA	M12	100 cm Cable 2-Core 7/0.2	Nitrile	UL
RSF58H100RC	PP (UL)	-20°C to +100°C	100VA	M12	100cm PVC 16/0.2	Nitrile	UL
RSF58H100R1/8	PP (UL)	-20°C to +100°C	100VA	1/8" NPT	100cm PVC 16/0.2	N/A	UL
RSF58Y100RC	PP (UL)	-20°C to +100°C	25VA	M12	100cm PVC 16/0.2	Nitrile	UL
RSF58Y100R1/8	PP (UL)	-20°C to +100°C	25VA	1/8" NPT	100cm PVC 16/0.2	N/A	UL

Custom versions can be made for particular applications. Please contact Sensata with your requirements.







Made in the UK

Sensata Technologies, Inc. ("Sensata") data sheets are solely intended to assist designers ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products. Sensata data sheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular data sheet. Sensata may make corrections, enhancements, improvements and other changes to its data sheets or components without notice.

Buyers are authorized to use Sensata data sheets with the Sensata component(s) identified in each particular data sheet. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENSATA DATA SHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATA SHEETS OR USE OF THE DATA SHEETS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATA SHEETS OR USE THEREOF.

All products are sold subject to Sensata's terms and conditions of sale supplied at <a href="https://www.sensata.com">www.sensata.com</a> SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

#### **CONTACT US**

+44 (0)1202 897969 support@sensata.com Sensata | Cynergy3 7 Cobham Road, Ferndown Industrial Estate, Wimborne, Dorset, BH21 7PE, United Kingdom