

Sling swivels, hoist rings

CARTEC

Application:

Attachment point for lifting loads.

Execution:

- Suitable for secure raising of loads according to Machinery Directive
- 2006/42/EC
- constructed, tested and certified according to GS-OA 15-04 – EN 1677
- DGUV certification
- Magnaflux crack tested to 100%
- can be rotated 360°

Advantage:

- load direction 90°, with minimal space requirement
- Durable corrosion protection of screw
- designed for a load of 20,000 load changes



Art. no.	77239 143
Brand	CARTEC
Manufacturer Part Number	C806X42
Thread dimension	M42
Load-carrying capacity	15 t
External width	169 mm
Internal width	97 mm
Width of support plate	85 mm
Bracket diameter	36 mm
Usable thread length	63 mm
Bracket height	242 mm
Width across flats	65 mm
Distance between lower edge of retainer holder and retainer	89 mm
Gross Weight	11.200 kg
Product Group	775

EAN

8013429871108