

RANA LED Recessed 1200

RANA LED R 1200 LO 3K LOUV+PRI W GEN2

0052422



Product features

- Ceiling Recessed LED Linear luminaire (lay-in), with Louvre + Prismatic Optic, Direct Light Distribution, Luminaire Dimensions: 1196x296x60mm, Sylvania White body colour, IP20, IK07, Light Engine Dimensions: 1130x65mm, Constant Current, Low LED flicker (+/-5%), Warm White (3000K) LED Colour Temperature, 2900lm, 28W, 104lm/W efficacy, CRI>80, 3 SDCM (3-step MacAdam ellipse) LED Colour Consistency, UGR<19, Luminance at 65° < 3000 cd/m2, Lumen Maintenance: L90B10 at 50,000 hours, Glow Wire Test 850°C, Quick and easy electrical connection with direct access to push-connectors on top, 2 x metallic safety cables (1.5m) included, the luminaire can be covered with building insulation of Glass Wool type.



PRODUCT OVERVIEW

Product name	RANA LED R 1200 LO 3K LOUV+PRI W GEN2
Technology	LED
Cap/Base	N/A
Housing	Steel
Mount	Ceiling recessed mounting
General application	Education, Hospitality, Office, Retail
ETIM Class	EC002892
E-number FI	4273782
Warranty	5 years
Fixture luminous flux (lm)	2900
Luminous flux (lm)	2900
Luminaire efficacy (lm/W)	104
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Glare control	< 19
Photobiological Risk Group	RG0
Total power consumption (W)	28
Electrical protection	Class I
Control gear type	LED driver constant current
Dimmable	No
Dimming method	N/A
LED Flickering Rate	Ultra low (5% or less)
Housing colour	White
IP rating	IP20
IK rating	IK07
Product EAN number	5410288524221

DATA TABLE

RANA LED Recessed 1200

RANA LED R 1200 LO 3K LOUV+PRI W GEN2
0052422

General data

Product name	RANA LED R 1200 LO 3K LOUV+PRI W GEN2
Technology	LED
Cap/Base	N/A
Housing	Steel
Mount	Ceiling recessed mounting
General application	Education, Hospitality, Office, Retail
Operating temperature range (°C)	5°C...+25°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
E-number FI	4273782
Warranty	5 years

Optical data

Fixture luminous flux (lm)	2900
Luminous flux (lm)	2900
Luminaire efficacy (lm/W)	104
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Distribution type	Symmetric
Glare control	< 19
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	28
Mains voltage (V)	220-240V
Lamp power factor	0.95
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	20
Electrical protection	Class I
Control gear required	No
Control gear type	LED driver constant current
Dimmable	No
Dimming method	N/A
Drive current (mA)	275
Inrush Current (A)	22
Inrush Duration (µs)	250
Glow Wire Test (°C)	850
Energy Efficiency Class (A->G) of contained light source	C
Nominal Frequency (Hz)	50/60Hz
LED Flickering Rate	Ultra low (5% or less)
Max. Luminaires per 10A C Breaker	28
Max. Luminaires per 13A C Breaker	36
Max. Luminaires per 16A C Breaker	45
Max. Luminaires per 20A C Breaker	56
Max. Luminaires per 10A B Breaker	17

RANA LED Recessed 1200

RANA LED R 1200 LO 3K LOUV+PRI W GEN2

0052422

Max. Luminaires per 13A B Breaker	22
Max. Luminaires per 16A B Breaker	27
Max. Luminaires per 20A B Breaker	34

Lifetime data

Lifespan L70 B50	50000
Lifespan L70 B10	50000
Lifespan L80 B50	50000
Lifespan L80 B10	50000
Lifespan L90 B50	50000
Lifespan L90 B10	50000

Physical data

Housing colour	White
IP rating	IP20
IK rating	IK07
Diffuser finish	Prismatic
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	1196
Nominal Product Width (mm)	296
Nominal Product Height (mm)	60
Weight (kg)	5.5
Recessed Depth (mm)	120

Packaging

Single packaging type	Carton
Product EAN number	5410288524221
Packaging single length / height (cm)	124.5
Packaging single width (cm)	6.5
Packaging single depth (cm)	32.0
DUN14 (outer)	05410288524221
Units per outer package	1
Packaging outer length / height (cm)	124.5
Packaging outer width (cm)	6.5
Packaging outer depth (cm)	32.0


Safety data

Optimal operating condition (°C)	5-25
----------------------------------	------

PHOTOMETRY

RANA LED Recessed 1200

RANA LED R 1200 LO 3K LOUV+PRI W GEN2
0052422



Distance [m]	Cone diameter [m]	E(0°)	E(C90)	E(C0)	Illuminance [lx]
0.5	0.96 0.86	6115	43.9° 1146	40.7° 1425	
1.0	1.92 1.72	1529	43.9° 287	42.7° 356	
1.5	2.89 2.58	679	43.9° 123	40.7° 158	
2.0	3.85 3.44	382	43.9° 72	42.7° 89	
2.5	4.81 4.30	245	43.9° 46	42.7° 57	
3.0	5.77 5.16	170	43.9° 32	42.7° 40	

Distance [m] Cone diameter [m] Illuminance [lx]
 C0 - C180 (Half beam angle: 81.4°)
 C90 - C270 (Half beam angle: 87.8°)

TECHNICAL DRAWINGS

