

## EC TYPE-EXAMINATION CERTIFICATE: 0805

**Product description: -** Personal Eye Protection- spectacles and goggles

**Product identification: -** See schedule

**Manufacturer: -** MSA Europe GmbH  
Schlüsselstrasse 12,  
8645 Jona,  
Switzerland

**When assessed and examined against harmonised standards EN166:1995 and EN166:2001 are found to be in conformity with Council Directive 89/686/EEC and associated amendments, relating to personal protective equipment.**


**Signed:**  ..... **Date:** 15<sup>th</sup> December 2014

K J Warren, Manager, Certification Services

**For and on behalf of INSPEC International Ltd.**  
56 Leslie Hough Way, Salford, Gt Manchester M6 6AJ, England (Notified Body No: 0194)

**Certification remains valid until 6<sup>th</sup> February 2018, providing compliance with INSPEC's terms and conditions is maintained.**

**Original date of issue: 15<sup>th</sup> March 2000**



For terms and conditions of issue, see page 2

## Terms and Conditions

Reference Documents: -

- |      |                          |   |   |  |
|------|--------------------------|---|---|--|
| i)   | Test Reports             | - | } | TF/449, TF/682, TF/687, TF/1055<br>TF/2429 |
| ii)  | Technical File           | - |   |  |
| iii) | Test and Inspection Plan | - |   |  |

Conditions attached to the issue of this certificate:

- i) Marking and instructions have been assessed in the English language only. It is the Manufacturers/Authorised Representatives responsibility to obtain and supply language versions acceptable to the country where the product is to be sold.
- ii) Any changes to the product, technical file or quality manual/quality plan shall be immediately notified to INSPEC.
- iii) The Manufacturer/Authorised Representative shall comply at all times with INSPEC's Regulations governing CE Product Certification.
- iv) This Certificate remains the property of INSPEC and may be withdrawn if any of the conditions attached to its issue are not complied with.
- v) This certificate may be copied or reproduced by the certificate holder, complete and without omissions or additions, and in accordance with INSPEC's terms of business.
- vi) This certificate has been provided in accordance with our standard Terms of Business, which can be viewed at, and printed from:

<http://inspec-international.com/ToB.pdf>

If you have difficulty accessing the Terms of Business, you may contact us for a copy.

# CERTIFICATION INDEX

Item	Status	Issued	Amendment
Page 1 of 2	Withdrawn		
Page 2 of 2	Withdrawn		
Schedule ONE	Withdrawn		
Schedule TWO	Withdrawn		
Page 2 of 2 (Amendment ONE)	Withdrawn		
Schedule THREE	Withdrawn		
Schedule FOUR	Withdrawn	31/1/06	To add Models :-Perspecta 2500 Perspecta 1320, Perspecta 2320
Page 1 of 2 Amendment (ONE)	Withdrawn		
Page 2 of 2 (Amendment TWO)	Withdrawn	31/1/06	To add TF/1055
Schedule FIVE	Withdrawn	12/7/06	To add Purple Blue lenses and Model :- Perspecta GIV2300, Perspecta 5060
Pages 1-4	Withdrawn	21/09/07	To add Lens options K & N for AF coating. Editorial changes.
Pages 1-4	Withdrawn	23/11/09	To add models as per amendment request dated 9/10/09
Pages 1 – 4	Withdrawn	120531	To add models Feather Fit, Blockz, Alaska, OvrG 2, Instinct
Page 1- 4	Withdrawn	130206	To add/change/delete models as per amendment request dated 25 <sup>th</sup> January 2013. Addition of 5 years validity
Page 1- 4	Valid	141215	To add models MOVE, TecTor and Motion Fit

# CERTIFICATION SCHEDULE

Model	Optical Class	Impact Level	Polycarbonate Lenses	Scale
<b>Spectacles</b>				
Perspecta 2047W	1	Low Energy @ Ext Temp (FT)	<div style="display: flex; align-items: center;"> <div style="font-size: 4em; margin-right: 10px;">}</div> <div> <p>Clear 2-1.2</p> <p>Clear 2C-1.2</p> <p>Smoke 5-2.5</p> <p>Dark Brown 5-2.5</p> <p>Green 3-3</p> <p>Amber 2-1.2</p> <p>Orange 2-1.7</p> <p>Orange Red 2-1.7</p> <p>Blue Purple 5-2</p> <p>Blue Mirror 5-2.5</p> <p>Light Gold Mirror 5-1.7</p> <p>Gold Mirror 5-2.5</p> <p>Silver Mirror 5-2.5</p> <p>Red Rainbow Mirror 5-3.1</p> </div> </div>	
Perspecta 1070	1	Low Energy @ Ext Temp (FT)		
Perspecta FL250	1	Low Energy @ Ext Temp (FT)		
Perspecta 1900	1	Low Energy @ Ext Temp (FT)		
Perspecta 9000	1	Low Energy @ Ext Temp (FT)		
Perspecta 010	1	Low Energy @ Ext Temp (FT)		
Perspecta 1320	1	Low Energy @ Ext Temp (FT)		
Perspecta 2320	1	Low Energy (F)		
Milan	1	Increased Robustness (S)		
Racers	1	Low Energy @ Ext Temp (FT)		
Alternator	1	Low Energy @ Ext Temp (FT)		
Altimeter	1	Low Energy @ Ext Temp (FT)		
Metropol	1	Low Energy @ Ext Temp (FT)		
FeatherFit	1	Low Energy @ Ext Temp (FT)		
Blockz	1	Low Energy @ Ext Temp (FT)		
Alaska	1	Low Energy @ Ext Temp (FT)		
OverG	1	Low Energy @ Ext Temp (FT)		
Instinct	1	Low Energy (F)		
MOVE	1	Low Energy @ Ext Temp (FT)		
TecTor	1	Low Energy (F)		
Motion Fit	1	Low Energy (F)		
<b>Goggles</b>				
Perspecta GH3001	1	Medium Energy (B)	<div style="display: flex; align-items: center;"> <div style="font-size: 4em; margin-right: 10px;">}</div> <div> <p>Clear 2-1.2/ 2C-1.2</p> <p>Clear 2-1.2</p> </div> </div>	
Perspecta GIV2300	1	Medium Energy @ Ext Temp (BT)		
FlexiChem PC	1	Medium Energy @ Ext Temp (BT349)		
FlexiChem	1	Low Energy @ Ext Temp (FT34)		
FlexiChem NV PC	1	Medium Energy @ Ext Temp (BT3459)		
FlexiChem NV	1	Low Energy @ Ext Temp (FT345)		
Responder	1	Medium Energy @ Ext Temp (BT3459)		
ChemPro	1	Medium Energy @ Ext Temp (BT349)		
Perspecta GV1000	1	Medium Energy (B)		
<b>Goggle Options</b>				
Liquid droplets (3), Large dust particles (4), Gas and fine dust particles < 5µm (5), Molten metal (9)				
<b>Following coating options are certified for all Spectacles and Goggles:</b>				
K (resistance to surface damage) – TuffStuff Antiscratch (AS)				
N (resistance to fogging) – Sightgard+plus Antifog (AF)				
K & N – OptiRock Antifog & Antiscratch. (AF, AS)				