


UGT592

Ultrasonic diffuse reflection sensor

UGQ00300EOKG/IO-Link/US



- 1 LEDs
2 teach button



Product characteristics

| | |
|-------------------------|--|
| Electrical design | PNP |
| Output function | normally open / normally closed; (parameterisable) |
| Sensing range [mm] | 40...300; (Target: 100 x 100 mm) |
| Communication interface | IO-Link |
| Housing | rectangular |
| Dimensions [mm] | M18 x 1 |

Electrical data

| | |
|-----------------------------|---|
| Operating voltage [V] | 10...30 DC; ("supply class 2" to cULus) |
| Current consumption [mA] | < 35 |
| Protection class | III |
| Reverse polarity protection | yes |
| Power-on delay time [s] | < 0.3 |
| Converter frequency [kHz] | 300 |

Inputs / outputs

| | |
|------------------------------|------------------------------|
| Number of inputs and outputs | Number of digital outputs: 1 |
|------------------------------|------------------------------|

UGT592



Ultrasonic diffuse reflection sensor

UGQ00300EOKG/IO-Link/US

| Outputs | | |
|---|------|---|
| Total number of outputs | | 1 |
| Electrical design | | PNP |
| Number of digital outputs | | 1 |
| Output function | | normally open / normally closed; (parameterisable) |
| Max. voltage drop switching output DC | [V] | 2.2 |
| Permanent current rating of switching output DC | [mA] | 100 |
| Switching frequency DC | [Hz] | 8 |
| Short-circuit protection | | yes |
| Overload protection | | yes |
| Detection zone | | |
| Sensing range | [mm] | 40...300; (Target: 100 x 100 mm) |
| Blind zone | [mm] | 40 |
| Angle of aperture cylindrical | [°] | 15; (± 2) |
| Max. deviation from the 90° angle sensor/object | [°] | ± 4 |
| Accuracy / deviations | | |
| Temperature compensation | | yes |
| Hysteresis | [%] | < 1 |
| Switch point drift | [%] | -2...2 |
| Linearity error of analogue output | [%] | ≤ 1 |
| Repeatability IO-Link | [%] | < 0,7 |
| Notes on the accuracy / deviation | | The indicated values are reached after a warm-up time of min. 20 minutes |
| Repeatability | | 1 % |
| Resolution | [mm] | 1 |
| Software / programming | | |
| Parameter setting options | | hysteresis / window; second switch point; Switch-on and switch-off delay; switch-on operations; Teach function; light-on/dark-on mode |

UGT592



Ultrasonic diffuse reflection sensor

UGQ00300EOKG/IO-Link/US

| Interfaces | | |
|-------------------------------|---|---|
| Communication interface | | IO-Link |
| Transmission type | | COM2 (38,4 kBaud) |
| IO-Link revision | | 1.1 |
| SDCI standard | | IEC 61131-9 |
| Profiles | | Smart Sensor: Device Identification; Multi-channel, two setpoint switching sensor, type 0 Generic Profiled Sensor; Process Data Variable; Device Diagnosis; Teach Channel |
| SIO mode | | yes |
| Required master port type | | A |
| Min. process cycle time [ms] | | 3.2 |
| IO-Link functions (cyclical) | | |
| | function | bit length |
| | process value | 16 |
| | device status | 4 |
| | binary switching information | 2 |
| IO-Link functions (acyclical) | | |
| | application specific tag; operating hours counter | |
| Supported DeviceIDs | | |
| | Type of operation | IO-Link device ID |
| | Default | 886 d / 00 03 76 h |
| Note | For further information please see the IODD PDF file at "Downloads" | |
| Operating conditions | | |
| Ambient temperature [°C] | | -20...70 |
| Storage temperature [°C] | | -30...80 |
| Protection | | IP 67 |
| Tests / approvals | | |
| EMC | EN 61000-4-2 ESD | 4 kV CD / 8 kV AD |
| | EN 61000-4-3 HF radiated | 3 V/m |
| | EN 61000-4-4 Burst | 2 kV |
| | EN 61000-4-6 HF conducted | 3 V |
| | EN 55011 | Class A |
| Vibration resistance | EN 60068-2-6 Fc | (10-55) Hz 1 mm amplitude, oscillation period 5 min., 30 min. per axis at resonance or 55 Hz |
| Shock resistance | EN 60068-2-27 Ea | 30 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes |
| MTTF [years] | | 197 |
| UL approval | Ta | -20...70 °C |
| | voltage supply | Class 2 |
| | File number UL | E174191 |
| Mechanical data | | |
| Weight [g] | | 97.5 |
| Housing | | rectangular |
| Dimensions [mm] | | M18 x 1 |
| Thread designation | | M18 x 1 |
| Materials | | 1.4542 (17-4 PH / 630); PBT; PA; epoxy glass ceramics |
| Tightening torque [Nm] | | 50 |

UGT592



Ultrasonic diffuse reflection sensor

UGQ00300EOKG/IO-Link/US

Displays / operating elements

| | | |
|----------------|--------------------------|-----------------------------------|
| Display | switching status echo | 1 x LED, yellow 1 x LED, green |
| Teach function | | yes |

Accessories

| | |
|------------------------|-------------------------------|
| Accessories (supplied) | lock nuts: 1, stainless steel |
|------------------------|-------------------------------|

Remarks


| | |
|---------------|---|
| Remarks | operating voltage "supply class 2" according to cULus |
| Pack quantity | 1 pcs. |

Electrical connection

Connector: 1 x M12



Connection





OUT: switching output / IO-Link

Ultrasonic diffuse reflection sensor

UGQ00300EOKG/IO-Link/US

Diagrams and graphs



- 1: distance
- 2: Detection zone
- 3: switch-on/switch-off graph
- 4: Target 100 x 100 mm
- 5: 50% of the target in the detection zone
- 6: switch point