


## Flow monitor

SID10ADBFPKG/US



- 1 LED bar display  
 2 setting pushbutton  
 3 Tightening torque 25 Nm



## Product characteristics

Number of inputs and outputs	Number of digital outputs: 2
Process connection	M18 x 1,5 internal thread

## Application

Media	Liquids; Gases
Medium temperature [°C]	-25...80
Pressure rating [bar]	300
Liquids	
Medium temperature [°C]	-25...80
Gases	
Medium temperature [°C]	-25...80

## Electrical data

Operating voltage [V]	19...36 DC
Current consumption [mA]	< 60
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	10

# SI0556



## Flow monitor

SID10ADBFPKG/US

Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2
Outputs		
Total number of outputs		2
Output signal		switching signal
Electrical design		PNP
Number of digital outputs		2
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Probe length L	[mm]	45
Liquids		
Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3..100
Gases		
Setting range	[cm/s]	200...3000
Greatest sensitivity	[cm/s]	200...800
Temperature monitoring		
Measuring range	[°C]	2...80
Resolution	[°C]	1
Accuracy / deviations		
Repeatability	[cm/s]	1...5
Note on repeatability		for water 5...100 cm/s; 25 °C Factory setting
Temperature drift	[cm/s x 1/K]	0.1; (for water 5...100 cm/s; 10...70 °C)
Temperature gradient	[K/min]	300
Switch point accuracy	[cm/s]	± 2...± 10; (for water 5...100 cm/s; 25 °C; Factory setting)
Hysteresis	[cm/s]	2...5; (for water 5...100 cm/s; 25 °C; Factory setting)
Temperature monitoring		
Switch point accuracy	[K]	± 3 (v > 5cm/s); (Liquids)
Resolution	[K]	1
Repeatability	[K]	2
Response times		
Response time	[s]	1...10
Liquids		
Response time	[s]	1...10

# SI0556



## Flow monitor

SID10ADBFPKG/US

### Gases

Response time	[s]	1...10
---------------	-----	--------

### Temperature monitoring

Response time	[s]	1...10
---------------	-----	--------

### Software / programming

Adjustment of the switch point	pushbutton
--------------------------------	------------

### Operating conditions

Ambient temperature	[°C]	-25...80
---------------------	------	----------

Storage temperature	[°C]	-25...100
---------------------	------	-----------

Protection		IP 67
------------	--	-------

### Tests / approvals

EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (55...2000 Hz)
MTTF	[years]	277

### Mechanical data

Weight	[g]	286
Dimensions	[mm]	M18 x 1.5
Thread designation		M18 x 1.5
Materials		stainless steel (1.4404 / 316L); stainless steel (1.4310 / 301); PC; PBT-GF20; EPDM/X
Materials (wetted parts)		stainless steel (1.4404 / 316L); O-ring: FKM 80 Shore A
Process connection		M18 x 1,5 internal thread

### Displays / operating elements

Display	function	10 x LED, three-colour
---------	----------	------------------------

### Remarks


Pack quantity	1 pcs.
---------------	--------

### Electrical connection

Connector: 1 x M12	
--------------------	--



### Connection



S1: Flow monitoring Temperature monitoring

S2: Temperature monitoring