SIEMENS

Data sheet

6ES7214-1HG40-0XB0



SIMATIC S7-1200, CPU 1214C, COMPACT CPU, DC/DC/RELAY, ONBOARD I/O: 14 DI 24V DC; 10 DO RELAY 2A; 2 AI 0 - 10V DC, POWER SUPPLY: DC 20.4 - 28.8 V DC, PROGRAM/DATA MEMORY: 75 KB

General information		
Engineering with		
Programming package	STEP 7 V13 SP1 or higher	
Diamlay		
Display with display	No	
with display	NO	
Supply voltage		
Rated value (DC)		
• 24 V DC	Yes	
permissible range, lower limit (DC)	20.4 V	
permissible range, upper limit (DC)	28.8 V	
Load voltage L+		
Rated value (DC)	24 V	
 permissible range, lower limit (DC) 	5 V	
 permissible range, upper limit (DC) 	250 V	
Input current		
Current consumption (rated value)	500 mA	
Current consumption, max.	1 500 mA	
Inrush current, max.	12 A; at 28.8 V	
Encoder supply		
24 V encoder supply		
• 24 V	L+ minus 4 V DC min.	
Output current		
Current output to backplane bus (DC 5 V), max.	1 600 mA; Max. 5 V DC for SM and CM	

Power losses	
Power loss, typ.	12 W
Memory	
Type of memory	EEPROM
Work memory	
Integrated	100 kbyte
• expandable	No
Load memory	
Integrated	4 Mbyte
 Plug-in (SIMATIC Memory Card), max. 	with SIMATIC memory card
Backup	
• present	Yes; maintenance-free
without battery	Yes
CPU processing times	0.005
for bit operations, typ.	0.085 μs; / instruction
for word operations, typ.	1.7 μs; / instruction
for floating point arithmetic, typ.	2.5 μs; / instruction
CPU-blocks	
Number of blocks (total)	DBs, FCs, FBs, counters and timers. The maximum number of addressable blocks ranges from 1 to 65535. There is no restriction, the entire working memory can be used
ОВ	
Number, max.	Limited only by RAM for code
Data areas and their retentivity	
retentive data area in total (incl. times, counters, flags), max.	10 kbyte
Flag	
Number, max.	8 kbyte; Size of bit memory address area
Process image	
Inputs, adjustable	1 kbyte
Outputs, adjustable	1 kbyte
Sulputo, adjustable	
Hardware configuration	
	3 comm. modules, 1 signal board, 8 signal modules
Hardware configuration	3 comm. modules, 1 signal board, 8 signal modules
Hardware configuration Number of modules per system, max.	3 comm. modules, 1 signal board, 8 signal modules
Hardware configuration Number of modules per system, max. Time of day	3 comm. modules, 1 signal board, 8 signal modules Yes
Hardware configuration Number of modules per system, max. Time of day Clock	
Hardware configuration Number of modules per system, max. Time of day Clock • Hardware clock (real-time clock)	Yes
Hardware configuration Number of modules per system, max. Time of day Clock • Hardware clock (real-time clock) • Deviation per day, max.	Yes 60 s/month at 25 °C

 of which, inputs usable for technological functions 	6; HSC (High Speed Counting)
integrated channels (DI)	14
m/p-reading	Yes
Number of simultaneously controllable inputs	
all mounting positions	
— up to 40 °C, max.	14
Input voltage	
Rated value (DC)	24 V
● for signal "0"	5 V DC at 1 mA
• for signal "1"	15 VDC at 2.5 mA
Input current	
● for signal "1", typ.	1 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— Parameterizable	0.2 ms, 0.4 ms, 0.8 ms, 1.6 ms, 3.2 ms, 6.4 ms and 12.8 ms, selectable in groups of four
— at "0" to "1", min.	0.2 ms
— at "0" to "1", max.	12.8 ms
for interrupt inputs	
— Parameterizable	Yes
for counter/technological functions	
— Parameterizable	Single phase: 3 @ 100 kHz & 3 @ 30 kHz, differential: 3 @ 80 kHz & 3 @ 30 kHz
Cable length	
• shielded, max.	500 m; 50 m for technological functions
• Unshielded, max.	300 m; For technological functions: No
Digital outputs	
Number of digital outputs	10; Relays
integrated channels (DO)	10
short-circuit protection	No; to be provided externally
Switching capacity of the outputs	
with resistive load, max.	2 A
● on lamp load, max.	30 W with DC, 200 W with AC
Output delay with resistive load	
• "0" to "1", max.	10 ms; max.
• "1" to "0", max.	10 ms; max.
Switching frequency	
• of the pulse outputs, with resistive load, max.	1 Hz
Relay outputs	
Number of relay outputs, integrated	10
Number of relay outputs	10

Number of operating cycles, max.	mechanically 10 million, at rated load voltage 100,000
Cable length	
• shielded, max.	500 m
Unshielded, max.	150 m
Analog inputs	
Number of analog inputs	2
Integrated channels (AI)	2; 0 to 10 V
Input ranges	
Voltage	Yes
Input ranges (rated values), voltages	
• 0 to +10 V	Yes
Input resistance (0 to 10 V)	≥100k ohms
Cable length	
• shielded, max.	100 m; twisted and shielded
Analog value creation	
Integration and conversion time/resolution per channel	
 Resolution with overrange (bit including sign), 	10 bit
max.	
 Integration time, parameterizable 	Yes
 Conversion time (per channel) 	625 µs
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
1st interface	
Interface type	PROFINET
	PROFINET Ethernet
Interface type	
Interface type Physics	Ethernet
Interface type Physics Isolated	Ethernet Yes
Interface type Physics Isolated Automatic detection of transmission speed	Ethernet Yes Yes
Interface type Physics Isolated Automatic detection of transmission speed Autonegotiation	Ethernet Yes Yes Yes
Interface type Physics Isolated Automatic detection of transmission speed Autonegotiation Autocrossing	Ethernet Yes Yes Yes
Interface type Physics Isolated Automatic detection of transmission speed Autonegotiation Autocrossing Functionality	Ethernet Yes Yes Yes Yes Yes
Interface type Physics Isolated Automatic detection of transmission speed Autonegotiation Autocrossing Functionality • PROFINET IO Device	Ethernet Yes Yes Yes Yes Yes Yes
Interface type Physics Isolated Automatic detection of transmission speed Autonegotiation Autocrossing Functionality • PROFINET IO Device • PROFINET IO Controller	Ethernet Yes Yes Yes Yes Yes Yes
Interface type Physics Isolated Automatic detection of transmission speed Autonegotiation Autocrossing Functionality • PROFINET IO Device • PROFINET IO Controller PROFINET IO Controller	Ethernet Yes Yes Yes Yes Yes Yes Yes
Interface type Physics Isolated Automatic detection of transmission speed Autonegotiation Autocrossing Functionality • PROFINET IO Device • PROFINET IO Controller PROFINET IO Controller • Transmission rate, max. • Number of connectable IO devices, max.	Ethernet Yes Yes Yes Yes Yes Yes Yes Your same seem of the seem
Interface type Physics Isolated Automatic detection of transmission speed Autonegotiation Autocrossing Functionality • PROFINET IO Device • PROFINET IO Controller PROFINET IO Controller • Transmission rate, max. • Number of connectable IO devices, max. • Prioritized startup	Ethernet Yes Yes Yes Yes Yes Yes Yes Your same seem of the seem
Interface type Physics Isolated Automatic detection of transmission speed Autonegotiation Autocrossing Functionality • PROFINET IO Device • PROFINET IO Controller PROFINET IO Controller • Transmission rate, max. • Number of connectable IO devices, max.	Ethernet Yes Yes Yes Yes Yes Yes 100 Mbit/s 16
Interface type Physics Isolated Automatic detection of transmission speed Autonegotiation Autocrossing Functionality PROFINET IO Device PROFINET IO Controller PROFINET IO Controller Transmission rate, max. Number of connectable IO devices, max. Prioritized startup — Number of IO Devices, max.	Ethernet Yes Yes Yes Yes Yes Yes 100 Mbit/s 16
Interface type Physics Isolated Automatic detection of transmission speed Autonegotiation Autocrossing Functionality • PROFINET IO Device • PROFINET IO Controller PROFINET IO Controller • Transmission rate, max. • Number of connectable IO devices, max. • Prioritized startup — Number of IO Devices, max. PROFINET IO Device	Ethernet Yes Yes Yes Yes Yes Yes 100 Mbit/s 16

— Number of IO controllers with shared device, max.

2

Communication functions	
S7 communication	
• supported	Yes
• as server	Yes
As client	Yes
Open IE communication	
• TCP/IP	Yes
• ISO-on-TCP (RFC1006)	Yes
• UDP	Yes
Web server	
• supported	Yes
User-defined websites	Yes
Number of connections	
• overall	16; dynamically
Test commissioning functions	
Status/control	Van
Status/control variable	Yes
 Variables 	Inputs/outputs, memory bits, DBs, distributed I/Os, timers, counters
Forcing	
• Forcing	Yes
Diagnostic buffer	
• present	Yes
Traces	
Number of configurable Traces	2; Up to 512 KB of data per trace are possible
Integrated Functions	
Number of counters	6
Counter frequency (counter) max.	100 kHz
Frequency meter	Yes
controlled positioning PID controller	Yes Yes
Number of alarm inputs	4
rumber of alami inputs	-
Galvanic isolation	
Galvanic isolation digital inputs	
 Galvanic isolation digital inputs 	500V AC for 1 minute
 between the channels, in groups of 	1

Galvanic isolation digital outputs

• between the channels

• Galvanic isolation digital outputs

Relays

No

2

Permissible potential difference	
between different circuits	500 V DC between 24 V DC and 5 V DC
EMC	
Interference immunity against discharge of static electri	city
Interference immunity against discharge of	Yes
static electricity acc. to IEC 61000-4-2	
Test voltage at air discharge	8 kV
Test voltage at contact discharge	6 kV
Interference immunity to cable-borne interference	
 Interference immunity on supply lines acc. to IEC 61000-4-4 	Yes
 Interference immunity on signal lines acc. to IEC 61000-4-4 	Yes
Surge immunity	
• on the supply lines acc. to IEC 61000-4-5	Yes
Immunity against conducted interference induced by hig	gh-frequency fields
 Interference immunity against high-frequency radiation acc. to IEC 61000-4-6 	Yes
Emission of radio interference acc. to EN 55 011	
Limit class A, for use in industrial areas	Yes; Group 1
• Limit class B, for use in residential areas	Yes; When appropriate measures are used to ensure compliance with the limits for Class B according to EN 55011
Degree and class of protection	
Degree of protection to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
CE mark	Yes
UL approval	Yes
cULus	Yes
RCM (formerly C-TICK)	Yes
FM approval	Yes
Marine approval	
Marine approval	Yes
Ambient conditions	
Free fall	
Drop height, max. (in packaging)	0.3 m; five times, in dispatch package
Ambient temperature in operation	
• Min.	-20 °C
• max.	60 °C; Number of simultaneously activated inputs or outputs 7 or 5 (no adjacent points) at 60 °C horizontal or 50 °C vertical, 14 or 10 at 55 °C horizontal or 45 °C vertical

 horizontal installation, min. 	-20 °C
 horizontal installation, max. 	60 °C
• vertical installation, min.	-20 °C
• vertical installation, max.	50 °C
Storage/transport temperature	
• Min.	-40 °C
• max.	70 °C
Air pressure acc. to IEC 60068-2-13	
Storage/transport, min.	660 hPa
 Storage/transport, max. 	1 080 hPa
 Permissible operating height 	-1000 to 2000 m
Relative humidity	
Operation, max.	95 %; no condensation
 Permissible range (without condensation) at 25 C 	95 %
Vibrations	
Vibrations	2G wall mounting, 1G DIN rail
 Operation, checked according to IEC 60068-2- 	Yes
Shock test	
• checked according to IEC 60068-2-27	Yes; IEC 68, Part 2-27 half-sine: strength of the shock 15 g (peak value), duration 11 ms
Pollutant concentrations	
— SO2 at RH < 60% without condensation	S02: < 0.5 ppm; H2S: < 0.1 ppm; RH < 60% condensation-free
programming	
Programming language	
— LAD	Yes
— FBD	Yes
— SCL	Yes
Cycle time monitoring	
• can be set	Yes
Dimensions	
Width	110 mm
Height	100 mm
Depth	75 mm
Depth Weights	75 mm
•	75 mm 435 g

6ES7214-1HG40-0XB0 Changes preserved
Page 7/7 12.03.2015 © Copyright Siemens AG