










# **Model Number**

# NMB2-12GM65-E2-FE-V1

# **Features**

- Stainless steel sensing face
- Sensing range 2 mm
- 3-wire DC
- Ferrous targets

# Connection



# **Pinout**



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	RK	(black)

# **Accessories**

V1-G-OR2M-POC Female cordset, M12, 4-pin, TPE cable, welding-bead resis-

# V1-G-2M-PUR

Cable socket, M12, 4-pin, PUR cable


## V1-W-2M-PUR

Cable socket, M12, 4-pin, PUR cable

### **AB-12**

Mounting aid

### **Dimensions**



# **Technical Data**

General specifications					
Switching element function		PNP I	NO		
Rated operating distance	s <sub>n</sub>	2 mm			
Installation		flush			
Output polarity		DC			
Assured operating distance	sa	0 1.62 mm	n		
Actuating element		Ferrous targ	jets		
Reduction factor r <sub>Al</sub>		0			
Reduction factor r <sub>Cu</sub>		0			
Reduction factor r <sub>304</sub>		0.25			
Reduction factor r <sub>316Ti</sub>		0.1			
Reduction factor r <sub>St37</sub>		1			
Reduction factor r <sub>Brass</sub>		0			

voininai ratings		
Operating voltage	$U_B$	10 30 V DC
Switching frequency	f	100 Hz
Hysteresis	Н	3 15 typ. 5 %
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	$U_d$	≤2 V DC
Operating current	IL.	≤ 200 mA
Current concumption		< 14 mΔ

≤ 10 μA

### Off-state current Functional safety related parameter

	•	•	
$MTTF_d$			990 a
Mission	Time (T <sub>M</sub> )		20 a
Diagnos	tic Coverage (E	OC)	0 %

# Indicators/operating means

Operating display	4-way dual LED
	Green: power
	Yellow: output

### **Ambient conditions**

Ambient temperature	-40 70 °C (-40 158 °F)
Mechanical specifications	

### V1 connector (M12 x 1), 4-pin Stainless steel 1.4305 / AISI 303 Stainless steel 1.4305 / AISI 303 Connection type Housing material Sensing face

### Protection degree IP67 / IP68 / IP69K - cordset dependent according to cable speci-

### Compliance with standards and directives

Standard conformity
---------------------

•	
Standards	EN 60947-5-2:2007
	IEC 60947-5-2:2007

## Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose
CCC approval	Products with a maximum operating voltage of ≤36 V do not bear a
	CCC marking because they do not require approval.