

# METRAL<sup>®</sup> POWER, HIGH POWER AND COAX CONNECTORS

### **OVERVIEW**

Metral<sup>®</sup> power, high power and coax connectors are standalone modules, end-to-end stackable with Metral<sup>®</sup> signal modules. The connectors are designed in accordance with IEC 61076-4-104 and Telcordia GR-1217-CORE.

Metral<sup>®</sup> power, high power and coax connectors support power solution with current rating of 3 to 40A for each pin. They are available in 4 and 5 row versions.

The power connector range featuring blade contacts is offered in vertical headers and right angle receptacles, right angle headers and vertical receptacles. The coax range includes single and multi pin versions.


Metral<sup>®</sup> backplane connectors meet Futurebus+ standards to support applications in data, industrial and instrumentation, medical and telecom markets.



#### **FEATURES**

Modular and scalable	<ul> <li>End-to-end stackable with other power, signal and coax modules</li> </ul>
<ul> <li>Varying pin length enables first-mate, last-break capability</li> </ul>	<ul> <li>Allows sequential connection of pins for design flexibility and offers protection</li> </ul>
Dual beam contact design for receptacles blade	Provides electrical reliability and withstands vibration
Current rating of 3 to 40A	Caters to different application requirement
<ul> <li>Power connector range with blade contacts uses same PCB footprint as signal modules</li> </ul>	Interchangeable solution offers design flexibility
<ul> <li>Press-fit, Solder-to-Board and Pin-in-Paste terminations available</li> </ul>	Caters to different application requirement
Power and coax couplers are available	Suitable for Rear Plug-Up (RPU) application
Mini coax connectors are available	Compact size and small footprint

**BENEFITS** 



### METRAL<sup>®</sup> POWER, HIGH POWER AND COAX CONNECTORS

### **TECHNICAL INFORMATION**

### MATERIALS

- Housing: High temperature thermoplastic; UL 94V-0
- Contact: Copper Alloy
- Plating: Performance-based plating

### **ELECTRICAL PERFORMANCE**

- Power
  - Dielectric Withstanding Voltage : 1000V rms
  - + Insulation Resistance: 5000M $\Omega$  min
  - Current Rating: 3-40A
- Coax
  - Electrical Impedance: 50  $\Omega$  and 75  $\Omega$
  - Operating Voltage: 250V
  - Insulation Resistance: 3000M $\Omega$  min

### **ENVIRONMENTAL**

- Power
  - Operating Temperature: -55°C to +125°C
- Coax
  - Operating Temperature: -65°C to +165°C

### **SPECIFICATIONS**

- Product Specifications: GS-12-180, GS-12-453
- Application Specifications: BUS-20-075, TA-941

## **PART NUMBERS**

### **METRAL® STANDARD POWER (3A)**

Right Angle Re	ceptacle (RAR)	Vertical Header (VH)		
Row		Termination	Row	
4	5		4	5
88949-102LF	89096-102LF	Press-fit	70236-101LF	89099-111LF
89039-101LF	85876-102LF	Solder-to- Board		
72651-101LF	63793-101LF	Pin-in- Paste		

### **MECHANICAL PERFORMANCE**

- Power
  - Mating Force : 1.5 N max. per pin
  - Unmating Force : 0.30 N min. per pin
- Coax
  - Mating Force: 0.9N
  - Unmating Force: 0.9N

### **APPROVALS AND CERTIFICATIONS**

- IEC 61076-4-104
- Telcordia GR-1217-CORE

### PACKAGING

- Tube for Press-fit and Solder to Board Terminations
- Tape and Reel for Pin-in-Paste Termination

### **TARGET MARKETS/APPLICATIONS**

- Data
- Industrial & Instrumentation
- Medical
- Telecom

### **METRAL® HIGH POWER (40A)**

Description	Part Numbers
Right angle receptacle housing	89092-101LF
Receptacle contact	85995-103LF
Wide body header housing	88911-101LF
Contact screw PCB	91570-001LF

### **METRAL® COAX**

Description	Part Numbers
Right angle receptacle housing	70244-102LF
Receptacle contact STB	70239-002LF
Wide body header housing	88913-101LF
Contact STB	88980-002LF

#### **Disclaimer** Please note that the above information is subject to change without notice.