

Neodymium Block Magnet

Typical Applications

- Neodymium iron boron 'rare earth' material
- Strongest magnet material available
- 80°C max. operating temp.
- High resistance to de-magnetisation
- Anisotropic
- N35 grade



Eclipse Magnetics Part Number	Description	Weight (g)	Pull Force (kg)
N859	20mm x 8mm x 3mm Neodymium block magnet	22.5	2.57
N860	10mm x 5mm x 2mm Neodymium block magnet	3.8	0.74
N861	10mm x 10mm x 5mm Neodymium block magnet	19	2.57
N862	20mm x 10mm x 2mm Neodymium block magnet	15.2	1.85
N863	20mm x 10mm x 5mm Neodymium block magnet	38	5